




**SLD 5.08V/22/90B 3.2 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

**General ordering data**

|              |                                                                                                                                                                                   |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male header, Dovetails for fixing blocks, THT solder connection, 5.08 mm, Number of poles: 22, 90°, Solder pin length (l): 3.2 mm, tinned, Pale green, Box |
| Order No.    | <a href="#">1013970000</a>                                                                                                                                                        |
| Type         | SLD 5.08V/22/90B 3.2 SN GN BX                                                                                                                                                     |
| GTIN (EAN)   | 4032248722068                                                                                                                                                                     |
| Qty.         | 10 items                                                                                                                                                                          |
| Product data | IEC: 320 V / 17 A<br>UL: 300 V / 10 A                                                                                                                                             |
| Packaging    | Box                                                                                                                                                                               |

## SLD 5.08V/22/90B 3.2 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                       |                            |
|-----------------------|----------------------------|
| ROHS                  | Conform                    |
| UL File Number Search | <a href="#">UL Website</a> |
| Certificate No. (UR)  | E60693                     |

## Dimensions and weights

|                          |          |                 |             |
|--------------------------|----------|-----------------|-------------|
| Depth                    | 22 mm    | Depth (inches)  | 0.8661 inch |
| Height                   | 28.7 mm  | Height (inches) | 1.1299 inch |
| Height of lowest version | 26.2 mm  | Width           | 58.42 mm    |
| Width (inches)           | 2.3 inch | Net weight      | 18.39 g     |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## System specifications

| Product family                               | OMNIMATE Signal - series BL/SL 5.08                 | Type of connection                         | Board connection             |
|----------------------------------------------|-----------------------------------------------------|--------------------------------------------|------------------------------|
| Mounting onto the PCB                        | THT solder connection                               | Pitch in mm (P)                            | 5.08 mm                      |
| Pitch in inches (P)                          | 0.200 "                                             | Outgoing elbow                             | 90°                          |
| Number of poles                              | 22                                                  | Number of solder pins per pole             | 1                            |
| Solder pin length (l)                        | 3.2 mm                                              | Solder pin length tolerance                | +0.1 / -0.3 mm               |
| Solder pin dimensions                        | d = 1.2 mm, Octagonal                               | Solder pin dimensions = d tolerance        | 0 / -0.03 mm                 |
| L1 in mm                                     | 50.80 mm                                            | L1 in inches                               | 2.000 "                      |
| Number of rows                               | 2                                                   | Pin series quantity                        | 2                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe unplugged/<br>back-of-hand-safe plugged | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Protection degree                            | IP20                                                | Volume resistance                          | ≤5 mΩ                        |
| Can be coded                                 | Yes                                                 | Plugging cycles                            | 25                           |

## Material data

|                                       |                                |                                       |                                |
|---------------------------------------|--------------------------------|---------------------------------------|--------------------------------|
| Insulating material                   | PBT                            | Colour                                | Pale green                     |
| Colour chart (similar)                | RAL 6021                       | Insulating material group             | IIla                           |
| Comparative Tracking Index (CTI)      | ≥ 200                          | Moisture Level (MSL)                  |                                |
| UL 94 flammability rating             | V-0                            | Contact material                      | Cu-alloy                       |
| Contact surface                       | tinned                         | Layer structure of solder connection  | 1...3 µm Ni / 2...4 µm Sn matt |
| Layer structure of plug contact       | 1...3 µm Ni / 2...4 µm Sn matt | Storage temperature, min.             | -40 °C                         |
| Storage temperature, max.             | 70 °C                          | Operating temperature, min.           | -50 °C                         |
| Operating temperature, max.           | 100 °C                         | Temperature range, installation, min. | -25 °C                         |
| Temperature range, installation, max. | 100 °C                         |                                       |                                |

## Rated data acc. to IEC

|                                               |                        |                                               |       |
|-----------------------------------------------|------------------------|-----------------------------------------------|-------|
| tested acc. to standard                       | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 17 A  |
| Rated current, max. number of poles (Tu=20°C) | 11 A                   | Rated current, min. number of poles (Tu=40°C) | 9.5 A |

**SLD 5.08V/22/90B 3.2 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**

Rated voltage for surge voltage class / 320 V  
pollution degree II/2

Rated voltage for surge voltage class / 250 V  
pollution degree III/3

Rated impulse voltage for surge voltage 4 kV  
class/ pollution degree III/2

Rated voltage for surge voltage class / 250 V  
pollution degree III/2

Rated impulse voltage for surge voltage 400 V  
class/ pollution degree II/2

Rated impulse voltage for surge voltage 4 kV  
class/ contamination degree III/3

**Rated data acc. to CSA**

|                                   |                                                                        |
|-----------------------------------|------------------------------------------------------------------------|
| Institute (CSA)                   | CSA                                                                    |
| Rated voltage (Use group B / CSA) | 300 V                                                                  |
| Rated current (Use group B / CSA) | 10 A                                                                   |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |                |
|-----------------------------------|----------------|
| Certificate No. (CSA)             | 200039-1121690 |
| Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group D / CSA) | 10 A           |

**Rated data acc. to UL 1059**

|                                       |                                                                        |
|---------------------------------------|------------------------------------------------------------------------|
| Institute (UR)                        | UR                                                                     |
| Rated voltage (Use group B / UL 1059) | 300 V                                                                  |
| Rated current (Use group B / UL 1059) | 10 A                                                                   |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |

|                                       |        |
|---------------------------------------|--------|
| Certificate No. (UR)                  | E60693 |
| Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group D / UL 1059) | 10 A   |

**Packing**

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 151.00 mm |
| VPE width | 135.00 mm | VPE height | 35.00 mm  |

**Important note**

|                |                                                                                                                                                                                                                                                                                                                                                                           |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                |
| Notes          | <ul style="list-style-type: none"> <li>In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |


## SLD 5.08V/22/90B 3.2 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Product image



## Dimensional drawing

