

**SCT-C 7.9/840****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Cable ties are characterised by maximum tying force and a long life. Steel cable ties also offer permanent fastening under extreme conditions such as high temperatures or severe chemical effects.

- Fully coated stainless steel cable ties
- Secure ball locking mechanism for a fast and simple installation
- Can be attached manually or using a tool
- These cables ties are recommended for special applications, such as for use with saline spray, extreme temperatures or corrosive surroundings.

**General ordering data**

Version	Cable ties, 7.9 x 840 mm, Stainless steel, polyester coated, 1112 N
Order No.	<a href="#">1015350000</a>
Type	SCT-C 7.9/840
GTIN (EAN)	4032248724321
Qty.	100 items

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E524836

## Dimensions and weights

Depth	1.1 mm	Depth (inches)	0.0433 inch
Height	840 mm	Height (inches)	33.0708 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	15.37 g		

## Temperatures

Operating temperature range	-80...150 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	165 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Installation materials

UV-resistant	Yes	For re-opening	No
UL 94 flammability rating	None	Operating temperature range, max.	150 °C
Operating temperature range, min.	-80 °C	Halogen	No
Cable diameter, max.	250 mm	Basic material	Stainless steel, polyester coated
Tensile strength	1112 N	Bundle diameter, max.	250 mm
Tensile strength (Pound-force)	250 lbf	Bundle diameter, min.	20 mm

## Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

**Drawing**

