

VG 21 HQ EMV68 11-15.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
Order No.	1016120000
Type	VG 21 HQ EMV68 11-15.5
GTIN (EAN)	4032248725595
Qty.	1 items

VG 21 HQ EMV68 11-15.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 39.6 g

Temperatures

Limit temperature -40 °C ... 130 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP b5ff1f66-ddba-4739-9fc0-0521ddb52139

General information

Outer cable diameter, max.	15 mm	Outer cable diameter, min.	11 mm
Operating temperature range, max.	135 °C	Operating temperature range, min.	-40 °C
Pitch of thread	0 mm	Halogen	halogen-free
AF size 1	30 mm	AF size	30 mm
Protection degree	IP68	Cable gland	PG 21
Basic material	Brass, nickel-plated	External thread	PG 21

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		