

VG 21 HQ MS68 11.5-15.5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**IP68**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

| | |
|------------|--|
| Version | Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated |
| Order No. | 1016100000 |
| Type | VG 21 HQ MS68 11.5-15.5 |
| GTIN (EAN) | 4032248725564 |
| Qty. | 1 items |

VG 21 HQ MS68 11.5-15.5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|------|
| Net weight | 37 g |
|------------|------|

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 130 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|--------------------------|
| RoHS Compliance Status | Compliant with exemption |
|------------------------|--------------------------|

| | |
|--------------------------------------|----|
| RoHS Exemption (if applicable/known) | 6c |
|--------------------------------------|----|

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

| | |
|------|--------------------------------------|
| SCIP | b5ff1f66-ddba-4739-9fc0-0521ddb52139 |
|------|--------------------------------------|

General information

| | |
|-----------------------------------|----------------------|
| Outer cable diameter, max. | 15.5 mm |
| Operating temperature range, max. | 135 °C |
| Pitch of thread | 0 mm |
| AF size 1 | 30 mm |
| Protection degree | IP68 |
| Basic material | Brass, nickel-plated |

| | |
|-----------------------------------|--------------|
| Outer cable diameter, min. | 11.5 mm |
| Operating temperature range, min. | -40 °C |
| Halogen | halogen-free |
| AF size | 30 mm |
| Cable gland | PG 21 |
| External thread | PG 21 |

Classifications

| | |
|-------------|-------------|
| ETIM 8.0 | EC000441 |
| ETIM 10.0 | EC000441 |
| ECLASS 15.0 | 27-14-08-01 |

| | |
|-------------|-------------|
| ETIM 9.0 | EC000441 |
| ECLASS 14.0 | 27-14-08-01 |

VG 21 HQ MS68 11.5-15.5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Plug housing, cable entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC HQM TSLU 1PG21 | Version |
| Order No. | 1003100000 | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4032248698035 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 21 |

Plug housing, cable entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC HQM TOLU 1PG21 | Version |
| Order No. | 1003080000 | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4032248698011 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 21 |