

WQL 5 WF10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 5
Order No.	1016870000
Type	WQL 5 WF10
GTIN (EAN)	4032248726530
Qty.	5 items

WQL 5 WF10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	163.2 mm	Height (inches)	6.4252 inch
Width	25 mm	Width (inches)	0.9842 inch
Net weight	127.8 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Copper - zinc	Colour	grey
----------------	---------------	--------	------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
----------------	-----------------	---------------------	-----------------

Dimensions

Pitch in mm (P)	33.80 mm	TS 35 offset	36 mm
-----------------	----------	--------------	-------

General

Number of poles	5	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

Rating data

Nominal current	265 A
-----------------	-------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		