Data sheet

SAIBWS-P-3A-4/6-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.
Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.
The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Version	Field attachable connector, M12
Order No.	1021310000
Type	SAIBWS-P-3A-4/6-M12
GTIN (EAN)	4032248734290
Qty.	1 items
Delivery status	Discontinued
Last order date	2025-05-30T00:00:00+02:00
Alternative product	SAIBWS-P-4A-4/6-M12

Data sheet

SAIBWS-P-3A-4/6-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Dimensions and weights

Net weight	22.44 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Imidazolidine-2-thione 96-45-7
SCIP	bcee35cf-c0f5-43d2-8daf-65ab0d08641a

Technical data customisable plug-in connectors

Number of poles	3	Coding	A-coded
Contact surface	CuSnZn	Type of connection	Screw connection
Housing main material	PA	Insulation resistance	108 Ω
Cable diameter, max.	6 mm	Cable diameter, min.	4 mm
Conductor cross-section, max.	0.75 mm²	Conductor cross-section, min.	0.14 mm²
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 50
Pollution severity	3	Gender of contact	Female
Shield connection	No	Threaded ring material	Diecast zinc
Temperature range of housing	-40 … +85 ° C		

General Info

Number of poles	3	Connection 1	M12
Connection 2	Screw	Housing main material	PA
Connection thread	M12	Contact surface	CuSnZn
Protection degree	IP67	Plugging cycles	≥ 50

Standards

Connector standard	IEC 61076-2-101

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

SAIBWS-P-3A-4/6-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

