

HDC S8/0 MAS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The MixMate series of connectors can simultaneously transmit high rated currents and voltages as well as signals. An axial screw can be used to secure the wire.
Axial screw connection / TOP connection

General ordering data

Version	HDC insert, Male, 690 V, 110 A, Number of poles: 8, Axial screw connection, Installation size: 8
Order No.	1023360000
Type	HDC S8/0 MAS
GTIN (EAN)	4032248739509
Qty.	1 items

HDC S8/0 MAS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Dimensions and weights

Depth	111 mm	Depth (inches)	4.3701 inch
Height	48.5 mm	Height (inches)	1.9094 inch
Width	34 mm	Width (inches)	1.3386 inch
Net weight	263.12 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3
SCIP	b67daa31-7dca-434d-8290-da7fb52f83a2

Chemical resistance	Substance	Acetone
	Chemical resistance	Resistant
	Substance	Ammonia, watery
	Chemical resistance	Conditionally resistant
	Substance	Petrol
	Chemical resistance	Resistant
	Substance	Benzene
	Chemical resistance	Resistant
	Substance	Diesel oil
	Chemical resistance	Conditionally resistant
	Substance	Acetic acid, concentrated
	Chemical resistance	Resistant
	Substance	Potassium hydroxide
	Chemical resistance	Conditionally resistant
	Substance	Methanol
	Chemical resistance	Conditionally resistant
	Substance	Motor oil
	Chemical resistance	Conditionally resistant
	Substance	Lye, diluted
	Chemical resistance	Resistant
Substance	Hydrochlorofluorocarbons	
Chemical resistance	Conditionally resistant	
Substance	Outdoor use	
Chemical resistance	Conditionally resistant	

Dimensions

Width	34 mm	Total length base	111 mm
Height of plug	48.5 mm		

HDC S8/0 MAS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General data

Number of poles	8		
Tightening torque	0.5 Nm		
Plugging cycles, silver	≥ 500		
Plugging cycles, gold	≥ 500		
Type of connection	Axial screw connection		
Installation size	8		
UL 94 flammability rating	V-0		
Volume resistance	≤ 1 mΩ		
Colour	beige		
Insulation resistance	1010 Ω		
Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)		
Insulating material group	IIIa		
Conductor cross-section	25 mm ²		
Tightening torque, max. PE connection	7 Nm		
Surface finish	Silver passivated		
Type	Male		
Pollution severity	3		
Tightening torque, min. PE connection	6 Nm		
Basic material	Copper alloy		
Series	MixMate		
Rated voltage (DIN EN 61984)	690 V		
Rated voltage according to UL/CSA	600 V AC/DC		
Rated impulse voltage (DIN EN 61984)	8 kV		
Rated current (DIN EN 61984)	110 A		
Rated current (UR)	Wire connection cross section AWG	AWG 8	
	Rated current	50 A	
	Wire connection cross section AWG	AWG 6	
	Rated current	65 A	
	Wire connection cross section AWG	AWG 4	
	Rated current	85 A	
	Rated current (cUR)	Wire connection cross section AWG	AWG 8
		Rated current	44 A
Wire connection cross section AWG		AWG 6	
Rated current		56 A	
Wire connection cross section AWG		AWG 4	
Rated current		66 A	
Wire connection cross section AWG		AWG 2	
Rated current		83 A	
Free from halogens	true		
Low smoke acc. DIN EN 45545-2	Yes		
BG	8		
Number of power contacts	8		

Connection data PE

Connection type PE	Screw connection, Miscellaneous	Stripping length PE connection	12 mm
Tightening torque, max. PE connection	7 Nm	Tightening torque, min. PE connection	6 Nm
Rated cross-section	25 mm ²	Wire cross section, AWG (PE), min.	AWG 8
Wire cross section, AWG (PE), max.	AWG 4		

Power contact

Type of connection, power contact	Axial screw connection	Number of poles, performance contact	8
Stripping length, performance contact	12 mm	Clamping range, power contact, max.	25 mm ²

HDC S8/0 MAS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Clamping range, power contact, min.	10 mm ²	Rated voltage (DIN EN 61984), power contact	690 V
Rated impulse voltage (DIN EN 61984), power contact	8 kV	Rated current (DIN EN 61984), power contact	110 A
Hexagon socket	4 mm		

Version

Wire connection cross section AWG, max.	AWG 4	Stripping length, rated connection	12 mm
Type of connection	Axial screw connection	Installation size	8
Volume resistance	≤1 mΩ	Clamping screw	M 8 x 0.75 mm
Wire connection cross section AWG, min.	AWG 8	Wire connection cross section, finely stranded, max.	25 mm ²
Wire connection cross section, finely stranded, min.	10 mm ²	Conductor cross-section, max.	25 mm ²
Conductor cross-section, min.	10 mm ²	Surface finish	Silver passivated
Basic material	Copper alloy	BG	8

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

HDC S8/0 MAS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

