

## KLIPPON STB 6 MS HT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Abbildung ähnlich

Ideally suited for the energy, process and transportation industries, the Klippon® STB enclosure series is the perfect complement to our existing Klippon® enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. the Lloyds Register and EN62208.

- Sheet steel 1.0330, powder-coated in RAL 7032
- Comes with a standard seal that is resistant to high temperatures - extended temperature range of -60°C to +120°C
- Approved according to Lloyds Register
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.



### General ordering data

Version	Klippon STB (Small Terminal Box), Empty enclosure, Sheet steel enclosure, Height: 250 mm, Width: 400 mm, Depth: 130 mm, Basic material: Sheet steel, Powder-coated, Pebble grey
Order No.	<a href="#">1025050000</a>
Type	KLIPPON STB 6 MS HT
GTIN (EAN)	4032248745265
Qty.	1 items

## KLIPPON STB 6 MS HT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	130 mm	Depth (inches)	5.1181 inch
Height	250 mm	Height (inches)	9.8425 inch
Width	400 mm	Width (inches)	15.748 inch
Mounting dimension - height	150 mm	Mounting dimension - width	425 mm
Net weight	5225 g		

### Temperatures

Operating temperature -60 °C...120 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

### Cable glands, left

M63	2	M12	64
M50	4	M16	33
M32	10	M25	16
M20	30	M40	6

### Cable glands, right

M25	10	M63	2
M16	21	M40	3
M50	2	M32	8
M20	18	M12	36

### Cable glands, top/bottom

M20	30	M12	64
M63	2	M40	6
M32	10	M25	16
M50	4	M16	33

### Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD) DE PS2620 160412 002ISS02 Certificate No. (LLOYDSREG) LR23307703TA  
 Approval conditions LR

### General information

Material thickness of cover 1.5 mm Material thickness of enclosure 1.5 mm  
 Operating temperature, max. 120 °C Operating temperature, min. -60 °C

**KLIPPON STB 6 MS HT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

Lid attachment	M5 hexagonal screw with slot and 10mm distance across flats	Standards	DIN 4102-12
Surface finish	Powder-coated	Impact resistance	10 J version standard
Protection degree	IP66	Basic material	Sheet steel
Seal material	Silicone	Integral fixing	TAS 20 rail welded to floor
Enclosure attachment	Welded-on mounting foot with 8-mm holes	Protection class (UL)	Type 4, Type 4X
Number of lid screws	4	Access opening: width	382 mm
Flange plate	No	Max. payload	70 kg
Lid	Yes	Access opening: height	230 mm
Areas of use	Transportation, Marine engineering, Process industry, Packaging industry		

**Housing earth**

Cross-section , max.	25 mm <sup>2</sup>	Earth, enclosure, cover	Welded-on M6 x 10 stainless-steel earth stud
Earth, enclosure, external	Welded-on M6 x 16 stainless-steel bolts	Earth, enclosure, internal	Welded-on M6 x 16 stainless-steel bolts

**horizontal assembly**

WDU 10 / ZDU 10	2x37	WDU 16 / ZDU 16	2x30
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x72	WDU 4 / ZDU 4	2x60
WDU 6 / ZDU 6	2x46		

**vertical assembly**

WDU 10 / ZDU 10	3x22	WDU 16 / ZDU 16	3x18
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x42	WDU 4 / ZDU 4	3x35
WDU 6 / ZDU 6	3x27		

**Important note**

Product information	The fire rating up to E90 acc. to DIN 4102-12 depends on concrete configurations / installations (details see "Declaration of Manufacturer" in "Downloads")		
---------------------	---	--	--

**Classifications**

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		

