

## SFC 3/30 MC NE BL


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

Advantages:

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the heights of 12 mm, 21 mm and 30 mm

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	SlimFix Clip, Conductor and cable markers, 3.5 - 7 mm, 30 x 12.5 mm, blue
Order No.	<a href="#">1025340000</a>
Type	SFC 3/30 MC NE BL
GTIN (EAN)	4032248746392
Qty.	60 items

**SFC 3/30 MC NE BL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	11.3 mm	Depth (inches)	0.4449 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	12.5 mm	Width (inches)	0.4921 inch
Net weight	1.65 g		

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.009 kg CO2 eq.	

**General data**

Material colour according to resistance code	6		
Type of printing	neutral		
Width	12.5 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	blue		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	30 x 5 mm		
Recommended industries compatible printer	Machinery <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-40...100 °C		

**Conductor and cable markers**

Halogen	No	Conductor cross-section, max.	10 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>	Conductor O.D., max.	7 mm
Conductor O.D., min.	3.5 mm	Conductor O.D.	3.5 - 7 mm
Cross-section for connected wire	4 - 10 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

