


**SCDV 3.81/10/90F 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Two-tier SCDV pin header for wave soldering.

- It allows you to use two interfaces on only one surface and with only one step in the work flow.
- Outlet direction: 90° (recumbent)
- Connections at two offset levels and with open access to each row.
- Space for labelling and coding
- Packed in cardboard box.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

**General ordering data**

Version	PCB plug-in connector, male header, Flange, THT solder connection, 3.81 mm, Number of poles: 10, 90°, Solder pin length (l): 3.2 mm, tinned, orange, Box
Order No.	<a href="#">1032610000</a>
Type	SCDV 3.81/10/90F 3.2SN OR BX
GTIN (EAN)	4032248771882
Qty.	50 items
Product data	IEC: 320 V / 17.5 A UL: 300 V / 11 A
Packaging	Box

## SCDV 3.81/10/90F 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	21.9 mm	Depth (inches)	0.8622 inch
Height	25.9 mm	Height (inches)	1.0197 inch
Height of lowest version	22.7 mm	Width	29.44 mm
Width (inches)	1.1591 inch	Net weight	7.64 g

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	bf6d7a85-f544-4ef5-9f0d-e42877c7f5e6

## System specifications

Product family	OMNIMATE Signal - series BC/SC 3.81										
Type of connection	Board connection										
Mounting onto the PCB	THT solder connection										
Pitch in mm (P)	3.81 mm										
Pitch in inches (P)	0.150 "										
Outgoing elbow	90°										
Number of poles	10										
Number of solder pins per pole	1										
Solder pin length (l)	3.2 mm										
Solder pin length tolerance	+0,02 / -0.2 mm										
Solder pin dimensions	d = 1.0 mm, Octagonal										
Solder pin dimensions = d tolerance	0 / -0,03 mm										
Solder eyelet hole diameter (D)	1.2 mm										
Solder eyelet hole diameter tolerance (D)+ 0,1 mm											
L1 in mm	15.24 mm										
L1 in inches	0.600 "										
Number of rows	2										
Pin series quantity	2										
Touch-safe protection acc. to DIN VDE 57 106	finger-safe unplugged/ back-of-hand-safe plugged										
Touch-safe protection acc. to DIN VDE 0470	IP20 plugged/ IP10 unplugged										
Volume resistance	≤5 mΩ										
Can be coded	Yes										
Plugging force/pole, max.	7.5 N										
Pulling force/pole, max.	5.5 N										
Tightening torque	<table> <tr> <td>Torque type</td> <td>Mounting screw, PCB</td> </tr> <tr> <td>Usage information</td> <td> <table> <tr> <td>Tightening torque</td> <td>min. 0.1 Nm</td> </tr> <tr> <td></td> <td>max. 0.15 Nm</td> </tr> <tr> <td>Recommended screw</td> <td>Part number <b>PTSC KA 2.2X4.5 WN1412</b></td> </tr> </table> </td> </tr></table>	Torque type	Mounting screw, PCB	Usage information	<table> <tr> <td>Tightening torque</td> <td>min. 0.1 Nm</td> </tr> <tr> <td></td> <td>max. 0.15 Nm</td> </tr> <tr> <td>Recommended screw</td> <td>Part number <b>PTSC KA 2.2X4.5 WN1412</b></td> </tr> </table>	Tightening torque	min. 0.1 Nm		max. 0.15 Nm	Recommended screw	Part number <b>PTSC KA 2.2X4.5 WN1412</b>
Torque type	Mounting screw, PCB										
Usage information	<table> <tr> <td>Tightening torque</td> <td>min. 0.1 Nm</td> </tr> <tr> <td></td> <td>max. 0.15 Nm</td> </tr> <tr> <td>Recommended screw</td> <td>Part number <b>PTSC KA 2.2X4.5 WN1412</b></td> </tr> </table>	Tightening torque	min. 0.1 Nm		max. 0.15 Nm	Recommended screw	Part number <b>PTSC KA 2.2X4.5 WN1412</b>				
Tightening torque	min. 0.1 Nm										
	max. 0.15 Nm										
Recommended screw	Part number <b>PTSC KA 2.2X4.5 WN1412</b>										

## Material data

Insulating material	PA GF	Colour	orange
Colour chart (similar)	RAL 2000	Insulating material group	II

## SCDV 3.81/10/90F 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Comparative Tracking Index (CTI)	≥ 550
UL 94 flammability rating	V-0
Contact surface	tinned
Storage temperature, max.	70 °C
Operating temperature, max.	120 °C
Temperature range, installation, max.	120 °C

Moisture Level (MSL)	
Contact material	Cu-alloy
Storage temperature, min.	-40 °C
Operating temperature, min.	-50 °C
Temperature range, installation, min.	-25 °C

## Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	17.5 A
Rated current, min. number of poles (Tu=40°C)	17 A	Rated voltage for surge voltage class / pollution degree II/2	320 V
Rated voltage for surge voltage class / pollution degree III/2	160 V	Rated voltage for surge voltage class / pollution degree III/3	160 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	2.5 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	2.5 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	2.5 kV	Short-time withstand current resistance	3 x 1s with 76 A

## Rated data acc. to CSA

Rated voltage (Use group B / CSA)	300 V	Rated voltage (Use group D / CSA)	300 V
Rated current (Use group B / CSA)	11 A	Rated current (Use group D / CSA)	10 A

## Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059)	300 V	Rated voltage (Use group D / UL 1059)	300 V
Rated current (Use group B / UL 1059)	11 A	Rated current (Use group D / UL 1059)	10 A

## Packing

Packaging	Box	VPE length	258.00 mm
VPE width	160.00 mm	VPE height	29.00 mm

## Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
----------------	--

Notes	<ul style="list-style-type: none"> <li>Additional variants on request</li> <li>Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>P on drawing = pitch</li> <li>In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul>
-------	---

## Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		


## **SCDV 3.81/10/90F 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## Product image



## Dimensional drawing

