


**DMC 12/27 MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

The DMC markers can be used for labelling switching devices or sub-assemblies. The large (12 x 27 mm) marking surface offers sufficient room for information describing the device and its function. Only one tag size for cable cross-sections from 0.5 – 10 mm<sup>2</sup> enables use on both multi-core control cables and single cores. For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	DMC, Device markers, 1.5 - 7.5 mm, 12 x 27 mm, To customer specification
Order No.	<a href="#">1038830000</a>
Type	DMC 12/27 MC SDR
GTIN (EAN)	4032248768080
Qty.	10 items

**DMC 12/27 MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	5 mm	Depth (inches)	0.1968 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.67 g		

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.018 kg CO2 eq.	

**General data**

Number per sheet	10		
Type of printing	To customer specification		
Printing method	MC Laser		
Width	27 mm		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	To customer specification		
Halogen	No		
Basic material	Polyamide 66		
Colour of printing	black		
Printed characters	Requires M-Print PRO File		
Advice label	Colour based on customer requirements (Please send M-Print PRO file)		
Number of markers per packaging unit	Form of supply	MultiCard	
compatible printer	<a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Device markers		
Operating temperature range	-40...100 °C		

**Device markers**

Halogen No

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		