



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**













1





Similar to illustration

Extra flat high-temperature-resistant two-tier SCDN-THR pin header for reflow soldering.


- Two compact interfaces are used with the flat BCF 3.81 (PUSH IN) socket block.
- Available as 90° (recumbent).
- Connections on a single level, allowing access that is flush over the front board.
- Space for labelling and coding
- Packed in cardboard box.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

### **General ordering data**

| Version      | PCB plug-in connector, male header, Flange,<br>THT/THR solder connection, 3.81 mm, Number<br>of poles: 22, 90°, Solder pin length (I): 1.5 mm,<br>tinned, black, Box |
|--------------|--|
| Order No.    | 1040270000   |
| Туре         | SCDN-THR 3.81/22/90F 1.5SN BK BX   |
| GTIN (EAN)   | 4032248768882  |
| Qty.         | 50 items   |
| Product data | IEC: 320 V / 17.5 A<br>UL: 300 V / 11 A  |
| Packaging    | Вох  |







### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| ROHS                                       | Conform                  |                       |                     |                |                             |
|--|--------------------------|-----------------------|---------------------|----------------|-----------------------------|
| Dimensions and weights                     |                          |                       |                     |                |                             |
|  |                          |                       |                     |                |                             |
| Depth                                      | 13.3 mm                  | Depth (inches)        |                     | .5236 inch     |                             |
| Height                                     | 16.7 mm                  | Height (inches)       |                     | .6575 inch     |                             |
| Height of lowest version                   | 15.2 mm                  | Width                 |                     | 2.3 mm         |                             |
| Width (inches)                             | 2.0591 inch              | Net weight            | 9.                  | .44 g          |                             |
| Environmental Product Compl                | liance                   |                       |                     |                |                             |
| RoHS Compliance Status                     | Compliant with exemption |                       |                     |                |                             |
| RoHS Exemption (if applicable/known)       | 6с                       | ·                     |                     |                |                             |
| REACH SVHC                                 | Lead 7439-92-1           |                       |                     |                |                             |
| SCIP                                       | 98f26c42-1118-4423-8e    | 88-c23hf260aaa0       |                     |                |                             |
|  | 00120072-1110-4420-06    | CZODIZOJAGAJ          |                     |                |                             |
| System specifications                      |                          |                       |                     |                |                             |
| Product family                             | OMNIMATE Signal - series | s BC/SC 3.81          |                     |                |                             |
| Type of connection                         | Board connection         |                       |                     |                |                             |
| Mounting onto the PCB                      | THT/THR solder connecti  | on                    |                     |                |                             |
| Pitch in mm (P)                            | 3.81 mm                  |                       |                     |                |                             |
| Pitch in inches (P)                        | 0.150 "                  |                       |                     |                |                             |
| Outgoing elbow                             | 90°                      |                       |                     |                |                             |
| Number of poles                            | 22                       |                       |                     |                |                             |
| Number of solder pins per pole             | 1                        |                       |                     |                |                             |
| Solder pin length (I)                      | 1.5 mm                   |                       |                     |                |                             |
| Solder pin length tolerance                | +0,02 / -0,02 mm         |                       |                     |                |                             |
| Solder pin dimensions                      | d = 1.0 mm, Octagonal    |                       |                     |                |                             |
| Solder pin dimensions = d tolerance        | 0 / -0,03 mm             |                       |                     |                |                             |
| Solder eyelet hole diameter (D)            | 1.3 mm                   |                       |                     |                |                             |
| Solder eyelet hole diameter tolerance (D   | 0)+ 0.1 mm               |                       |                     |                |                             |
| Outside diameter of solder pad             | 2.1 mm                   |                       |                     |                |                             |
| remplate aperture diameter                 | 1.9 mm                   |                       |                     |                |                             |
| 1 in mm                                    | 38.10 mm                 |                       |                     |                |                             |
| _1 in inches                               | 1.500 "                  |                       |                     |                |                             |
| Number of rows                             | 2                        |                       |                     |                |                             |
| Pin series quantity                        | 2                        |                       |                     |                |                             |
| Fouch-safe protection acc. to DIN VDE      | finger-safe unplugged/ba | ck-of-hand-safe plugg | ged                 |                |                             |
| Fouch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplu | ıgged                 |                     |                |                             |
| /olume resistance                          | ≤5 mΩ                    |                       |                     |                |                             |
| Can be coded                               | Yes                      |                       |                     |                |                             |
| Tightening torque                          | Torque type              |                       | Mounting screw, PCB |                |                             |
|  | Usage information        |                       | Tightening torque   | min.           | 0.1 Nm                      |
|  |                          |                       |                     | max.           | 0.15 Nm                     |
|  |                          |                       | Recommended screw   | Part<br>number | PTSC KA<br>2.2X4.5<br>WN141 |

#### **Material data**

| Insulating material    | LCP GF   | Colour                    | black |
|------------------------|----------|---------------------------|-------|
| Colour chart (similar) | RAL 9011 | Insulating material group | Illa  |

Creation date 06.11.2025 08:38:08 MEZ

Catalogue status / Drawings 2





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| Comparative Tracking Index (CTI)      | ≥ 175  | Moisture Level (MSL)                  | 1            |
|---------------------------------------|--------|---------------------------------------|--------------|
| UL 94 flammability rating             | V-0    | Contact material                      | Copper alloy |
| Contact surface                       | tinned | Storage temperature, min.             | -40 °C       |
| Storage temperature, max.             | 70 °C  | Operating temperature, min.           | -50 °C       |
| Operating temperature, max.           | 120 °C | Temperature range, installation, min. | -25 °C       |
| Temperature range, installation, max. | 120 °C |                                       |              |

### Rated data acc. to IEC

| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
|---|------------------------|---|------------------|
| Rated current, max. number of poles (Tu=20°C)                             | 13.2 A                 | Rated current, min. number of poles (Tu=40°C)                         | 17 A             |
| Rated current, max. number of poles (Tu=40°C)                             | 12.2 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

#### Rated data acc. to CSA

| Rated voltage (Use group B / CSA) | 300 V | Rated voltage (Use group D / CSA) | 300 V |
|-----------------------------------|-------|-----------------------------------|-------|
| Rated current (Use group B / CSA) | 11 A  | Rated current (Use group D / CSA) | 10 A  |

## Rated data acc. to UL 1059

| Rated voltage (Use group B / UL 1059) 300 V | Rated voltage (Use group D / UL 1059) 300 V |
|---|---|
| Rated current (Use group B / UL 1059) 11 A  | Rated current (Use group D / UL 1059) 10 A  |

#### **Packing**

| Packaging | Box       | VPE length | 280.00 mm |
|-----------|-----------|------------|-----------|
| VPE width | 255.00 mm | VPE height | 28.00 mm  |

### **Important note**

| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.   |
|----------------|--|
| Notes          | <ul> <li>Additional variants on request</li> <li>Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>P on drawing = pitch</li> <li>In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or</li> </ul> |

disengaged when live or under load
• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

## Classifications

| ETIM 6.0   | EC002637    | ETIM 7.0    | EC002637    |
|------------|-------------|-------------|-------------|
| ETIM 8.0   | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0  | EC002637    | ECLASS 9.0  | 27-44-04-02 |
| ECLASS 9.1 | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |

Creation date 06.11.2025 08:38:08 MEZ

Catalogue status / Drawings





### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |
|-------------|-------------|-------------|-------------|
| ECLASS 13.0 | 27-46-02-01 | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

Catalogue status / Drawings 4






Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Drawings**

# **Dimensional drawing**







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

**Coding elements** 



Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery. Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

#### **General ordering data**

| Туре              | SC-SMT 3.81 KO BK BX               | Version   |
|-------------------|------------------------------------|---|
| Order No.         | 2460700000                         | PCB plug-in connector, Accessories, Coding element, black         |
| GTIN (EAN)        | 4050118480023                      |   |
| Qty.              | 100 ST                             |   |
|                   |                                    |   |
| Type              | SC-SMT 3.81 KO WT BX               | Version   |
| Type<br>Order No. | SC-SMT 3.81 KO WT BX<br>2467670000 | Version PCB plug-in connector, Accessories, Coding element, white |
|                   |                                    |   |
| Order No.         | 2467670000                         |   |