


ESG X20 MC SDR**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Similar to illustration

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 10 mm, PA 66, Colour: To customer specification, pluggable
Order No.	1038890000
Type	ESG X20 MC SDR
GTIN (EAN)	4032248768141
Qty.	224 items

ESG X20 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	2.5 mm	Height (inches)	0.0984 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	0.02 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.001 kg CO2 eq.

General data

Printing method	MC Laser
Version	pluggable
Width	10 mm
UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C
Colour	To customer specification
Halogen	No
Basic material	PA 66
Colour of printing	black
Printed characters	Requires M-Print PRO File
Number of markers per packaging unit	Form of supply MultiCard
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2
Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...100 °C
Application/manufacturer	B&R X20 System

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		