


SCDN 3.81/06/90F 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image

Extra flat two-tier SCDN pin header for wave soldering.

- Two compact interfaces are used with the flat BCF 3.81 (PUSH IN) socket block.
- Available as 90° (recumbent).
- Connections on a single level, allowing access that is flush over the front board.
- Space for labelling and coding
- Packed in cardboard box.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

General ordering data

Version	PCB plug-in connector, male header, Flange, THT solder connection, 3.81 mm, Number of poles: 6, 90°, Solder pin length (l): 3.2 mm, tinned, black, Box
Order No.	1041310000
Type	SCDN 3.81/06/90F 3.2SN BK BX
GTIN (EAN)	4032248770113
Qty.	50 items
Product data	IEC: 320 V / 17.5 A UL: 300 V / 11 A
Packaging	Box

SCDN 3.81/06/90F 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	13.3 mm	Depth (inches)	0.5236 inch
Height	18.4 mm	Height (inches)	0.7244 inch
Height of lowest version	15.2 mm	Width	21.82 mm
Width (inches)	0.8591 inch	Net weight	5 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	cad4723c-c5fc-4802-be22-8cbcef126ab4

System specifications

Product family	OMNIMATE Signal - series BC/SC 3.81										
Type of connection	Board connection										
Mounting onto the PCB	THT solder connection										
Pitch in mm (P)	3.81 mm										
Pitch in inches (P)	0.150 "										
Outgoing elbow	90°										
Number of poles	6										
Number of solder pins per pole	1										
Solder pin length (l)	3.2 mm										
Solder pin length tolerance	+0,02 / -0,2 mm										
Solder pin dimensions	d = 1.0 mm, Octagonal										
Solder pin dimensions = d tolerance	0 / -0,03 mm										
Solder eyelet hole diameter (D)	1.2 mm										
Solder eyelet hole diameter tolerance (D)+ 0,1 mm											
L1 in mm	7.62 mm										
L1 in inches	0.300 "										
Number of rows	2										
Pin series quantity	2										
Touch-safe protection acc. to DIN VDE 57 106	finger-safe unplugged/ back-of-hand-safe plugged										
Touch-safe protection acc. to DIN VDE 0470	IP20 plugged/ IP10 unplugged										
Volume resistance	≤5 mΩ										
Can be coded	Yes										
Tightening torque	<table> <tr> <td>Torque type</td> <td>Mounting screw, PCB</td> </tr> <tr> <td>Usage information</td> <td> <table> <tr> <td>Tightening torque</td> <td>min. 0.1 Nm</td> </tr> <tr> <td></td> <td>max. 0.15 Nm</td> </tr> <tr> <td>Recommended screw</td> <td>Part number PTSC KA 2.2X4.5 WN1412</td> </tr> </table> </td> </tr> </table>	Torque type	Mounting screw, PCB	Usage information	<table> <tr> <td>Tightening torque</td> <td>min. 0.1 Nm</td> </tr> <tr> <td></td> <td>max. 0.15 Nm</td> </tr> <tr> <td>Recommended screw</td> <td>Part number PTSC KA 2.2X4.5 WN1412</td> </tr> </table>	Tightening torque	min. 0.1 Nm		max. 0.15 Nm	Recommended screw	Part number PTSC KA 2.2X4.5 WN1412
Torque type	Mounting screw, PCB										
Usage information	<table> <tr> <td>Tightening torque</td> <td>min. 0.1 Nm</td> </tr> <tr> <td></td> <td>max. 0.15 Nm</td> </tr> <tr> <td>Recommended screw</td> <td>Part number PTSC KA 2.2X4.5 WN1412</td> </tr> </table>	Tightening torque	min. 0.1 Nm		max. 0.15 Nm	Recommended screw	Part number PTSC KA 2.2X4.5 WN1412				
Tightening torque	min. 0.1 Nm										
	max. 0.15 Nm										
Recommended screw	Part number PTSC KA 2.2X4.5 WN1412										

Material data

Insulating material	PA GF	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	II
Comparative Tracking Index (CTI)	≥ 550	Moisture Level (MSL)	
UL 94 flammability rating	V-0	Contact material	Cu-alloy

SCDN 3.81/06/90F 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Contact surface	tinned	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	120 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	120 °C		

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	17.5 A
Rated current, max. number of poles (Tu=20°C)	13.2 A	Rated current, min. number of poles (Tu=40°C)	17 A
Rated current, max. number of poles (Tu=40°C)	12.2 A	Rated voltage for surge voltage class / pollution degree II/2	320 V
Rated voltage for surge voltage class / pollution degree III/2	160 V	Rated voltage for surge voltage class / pollution degree III/3	160 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	2.5 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	2.5 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	2.5 kV	Short-time withstand current resistance	3 x 1s with 76 A

Rated data acc. to CSA

Rated voltage (Use group B / CSA)	300 V	Rated voltage (Use group D / CSA)	300 V
Rated current (Use group B / CSA)	11 A	Rated current (Use group D / CSA)	10 A

Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059)	300 V	Rated voltage (Use group D / UL 1059)	300 V
Rated current (Use group B / UL 1059)	11 A	Rated current (Use group D / UL 1059)	10 A

Packing

Packaging	Box	VPE length	25.00 mm
VPE width	130.00 mm	VPE height	240.00 mm

Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
Notes	<ul style="list-style-type: none"> Additional variants on request Rated current related to rated cross-section & min. No. of poles. Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. P on drawing = pitch In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months


Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

SCDN 3.81/06/90F 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Product image****Dimensional drawing**