

## IE-C5DD4UG0350MCSA70-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12-RJ45

### General ordering data

Version	Dragline cable, PROFINET, M12 D-code – IP 67 straight pin, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 35 m
Order No.	<a href="#">1044470350</a>
Type	IE-C5DD4UG0350MCSA70-E
GTIN (EAN)	4064675022442
Qty.	1 items

## IE-C5DD4UG0350MCSA70-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Length	35 m	Length (inches)	1377.9528 inch
Net weight	2220.65 g		

### Temperatures

Storage temperature	-50 °C...70 °C	Operating temperature	
Installation temperature	-20 °C...60 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

### Cable specific standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, wire material	DIN EN 13602 Cu-ETP-A
Standard, shielding material	DIN EN 13602 Cu-ETP-A..B		

### Standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, wire material	DIN EN 13602 Cu-ETP-A
Standard, shielding material	DIN EN 13602 Cu-ETP-A..B		

### Cable structure

Strands	7	Sheathing colour	green (RAL 6018)
Standard designations	2YH(ST)C11Y 2x2x0,75/1,5-100 LI VZN GN FRNC	Cross-section	4*AWG 22/7 - 0.32 mm <sup>2</sup>
Shielding	SF/UTP	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Material sheath	PUR
Filler	As central element	Arrangement of wire cores	Star-quad
Wire core insulation thickness	0.38 mm	Complete shielding	Aluminium foil, Shielding braid made from copper wiring
Overlap of shielding braid	85 %	Wire material	Stranded tin-plated copper wire
Diameter of inner sheathing	3.9 mm	Sheathing material thickness	0.9 mm
Colour sequence or wires - wire pairs	white, yellow, blue, orange	Shielding braid thickness	0.13 mm

### Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Speed	180 m/min
Capacity at 1 kHz	52 nF/km	Loop resistance	120 Ω/km

## IE-C5DD4UG0350MCSA70-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

Test voltage: wire-wire-shield	2000 Veff, 50 Hz, 1 min	Resistance differential	3 %
Operating voltage, UL	600 V	Delay skew	40 ns/100m
Operating voltage (UL rating)	600 V	Transfer impedance	20 mΩ/m at 10 MHz
Characteristic impedance	100 ± 15 Ω at 1–100 MHz		

### Mechanical and material properties of cable

Resistance to oils	in accordance with IEC 60811-2-1	Silicone-free	Yes
Pulling force	≤ 150 N	Halogen	halogen-free, according to IEC 60754-2
Acceleration	4 m/s <sup>2</sup>	Min. bending radius, repetitive	7.5 x cable diameter
Min. bending radius, once only	5 x cable diameter	Abrasion resistance	very good
Bending cycles	3 Mio	Resistance to spread of flame	in accordance with IEC 60332-1
Speed	180 m/min	Fire propagation	No

### Plug, left

Plug left	M12, IP67, male contact, straight, plug, Plastic, shielded
-----------	--

### Plug, right

Plug right	RJ45, IP20, male contact, straight, plug, Plastic, shielded
------------	---

### Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Dimensioned drawing

Dimensioned drawing



Wiring

RJ45		M12
1	yellow	1
3	white	2
2	orange	3
6	blue	4