

## WS 10/6 PLUS MC NE WS


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.

WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |   |
|------------|---|
| Version    | WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, white |
| Order No.  | <a href="#">1046390000</a>  |
| Type       | WS 10/6 PLUS MC NE WS   |
| GTIN (EAN) | 4032248782109   |
| Qty.       | 600 items   |

**WS 10/6 PLUS MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 10 mm  | Height (inches) | 0.3937 inch |
| Width      | 6 mm   | Width (inches)  | 0.2362 inch |
| Net weight | 0.13 g |                 |             |

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

|                          |                             |                 |  |
|--------------------------|-----------------------------|-----------------|--|
| RoHS Compliance Status   | Compliant without exemption |                 |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                 |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2eq. |  |

**General data**

|   |   |           |  |
|---|---|-----------|--|
| Material colour according to resistance code            | 9   |           |  |
| Width   | 6 mm  |           |  |
| UL 94 flammability rating                               | V-2   |           |  |
| Operating temperature range, max.                       | 100 °C  |           |  |
| Operating temperature range, min.                       | -40 °C  |           |  |
| Colour  | white   |           |  |
| Halogen   | No  |           |  |
| Basic material  | Polyamide 66  |           |  |
| Printed characters                                      | neutral   |           |  |
| Number of markers per packaging unit compatible printer | Form of supply  | MultiCard |  |
|   | <a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a> |           |  |
| Number of markers per combination                       | 1 MultiCard = Terminal marker                             |           |  |
| Operating temperature range                             | -40...100 °C  |           |  |
| Application/manufacturer                                | Weidmueller, Allen-Bradley                                |           |  |

**Connector markers**

Pitch in mm (P) 6.00 mm

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**



**Drawing**

