

VG16 HQ K68 9-12SH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Polycarbonate
Order No.	1045530000
Type	VG16 HQ K68 9-12SH
GTIN (EAN)	4032248779437
Qty.	50 items

VG16 HQ K68 9-12SH

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 7.51 g

Temperatures

Limit temperature -20 °C ... 100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Outer cable diameter, max.	12 mm	Outer cable diameter, min.	9 mm
Operating temperature range, max.	135 °C	Operating temperature range, min.	-40 °C
Pitch of thread	0 mm	Halogen	halogen-free
AF size 1	27 mm	AF size	30 mm
Protection degree	IP68	Cable gland	PG 16
Basic material	Polycarbonate	External thread	PG 16

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		