## **WQV 10/3**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### **Product image**









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

#### **General ordering data**

Cross-connector (terminal), when screwed in, yellow, 63 A, Number of poles: 3, Pitch in mm (P): 9.90, Insulated: Yes, Width: 7.55 mm	
<u>1054960000</u>	
WQV 10/3	
4008190079079	
50 items	



# **WQV 10/3**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Approvals			
ROHS	Conform		
Dimensions and weights			
Danth	10	Donath (in all a c)	0.7007 in ab
Depth Height	18 mm 26.8 mm	Depth (inches) Height (inches)	0.7087 inch 1.0551 inch
Width	7.55 mm	Width (inches)	0.2972 inch
Net weight	5.5 g	- vidir (monos)	0.2072 Mon
Temperatures			
Characteristics	25 °C 55 °C	Andrianthannantun	F %C 40 %C
Storage temperature Continuous operating temp., min.	-25 °C55 °C -60 °C	Ambient temperature Continuous operating temp., max.	-5 °C40 °C 130 °C
Environmental Product Con		Continuous operating temp., max.	130 C
RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Material data			
Basic material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		
System specifications			
Version	For the terminals		
Additional technical data			
Tune of fixing	when coroused in	Installation advice	Direct mounting
Type of fixing	when screwed in	Installation advice	Direct mounting
Dimensions			
Pitch in mm (P)	9.90 mm		
General			
Number of poles	3	Installation advice	Direct mounting
Rating data			
Nominal current	63 A		
Classifications			
ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

Creation date 29.11.2025 06:59:53 MEZ

Catalogue status / Drawings 2