

## IE-BSS-V14M-SCRJ-SM-C

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



PushPull plug-in connector set according to IEC  
61076-3-117 ver.14 (PROFINET), metal incl. SC insert

### General ordering data

Version	Flange FO, IP67, Variant 14 standardized flange, SCRJ Duplex coupling, Singlemode
Order No.	<a href="#">1058 140000</a>
Type	IE-BSS-V14M-SCRJ-SM-C
GTIN (EAN)	403224879925 1
Qty.	10 items

## IE-BSS-V14M-SCRJ-SM-C

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform  
 UL File Number Search [UL Website](#)  
 Certificate no. (cULus) E316369

### Dimensions and weights

Depth	36.15 mm	Depth (inches)	1.4232 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	22.2 mm	Width (inches)	0.874 inch
Net weight	26.69 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

### General data

Description of article	Variant 14 standardized flange, SCRJ Duplex coupling	Colour	Miscellaneous
Housing main material	Zinc diecast	Type of mounting	2 screws
Protection degree	IP67	Plugging cycles	500
Fibre type	Singlemode	Insertion loss	≤ 0.5 dB
Connection 1	SCRJ	Connection 2	SCRJ
Return loss (attenuation)	≥ 40 dB		

### General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24	Certificate no. (cULus)	E316369
--------------------	---------------------------------------	-------------------------	---------

### Classifications

ETIM 8.0	EC000752	ETIM 9.0	EC000752
ETIM 10.0	EC000752	ECLASS 14.0	19-17-01-16
ECLASS 15.0	19-17-01-16		

**IE-BSS-V14M-SCRJ-SM-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Installation cut-out**

