


THM GEW 17/9 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

Version	THM, Device markers, 9 x 17 mm, yellow
Order No.	1059810000
Type	THM GEW 17/9 GE
GTIN (EAN)	4032248808229
Qty.	1 items

THM GEW 17/9 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.0118 inch
Height	9 mm	Height (inches)	0.3543 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	595 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Natural rubber adhesive	
Material colour according to resistance code	4	
Number per sheet	10000	
Printing method	Thermal transfer	
Version	Self-adhesive	
Width	17 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-29 °C	
Colour	yellow	
Halogen	Yes	
Basic material	Cotton fabric	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969 compatible printer	No	
	THM MULTIMARK , THM MULTIMARK PLUS	
Number of markers per combination	1 Label reel = Device markers	
Operating temperature range	-29...80 °C	
Number per roll	10000	

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings





THM GEW 17/9 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		