

WQB-PEN 16**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, Silver grey, 76 A, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: No, Width: 17.6 mm
Order No.	1060200000
Type	WQB-PEN 16
GTIN (EAN)	4008190112653
Qty.	10 items

WQB-PEN 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.0472 inch
Height	21.55 mm	Height (inches)	0.8484 inch
Width	17.6 mm	Width (inches)	0.6929 inch
Net weight	4.94 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material tinned copper Colour Silver grey

System specifications

Version Cross-connector

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
Explosion-tested version No Type of mounting when screwed in

Dimensions

Pitch in mm (P) 12.00 mm

General

Number of poles 2 Installation advice Direct mounting

Rating data

Rated voltage 400 V Nominal current 76 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		