


THM GEW 17/9 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

Version	THM, Device markers, 9 x 17 mm, yellow
Order No.	1059810000
Type	THM GEW 17/9 GE
GTIN (EAN)	4032248808229
Qty.	1 items

THM GEW 17/9 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.0118 inch
Height	9 mm	Height (inches)	0.3543 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	595 g		

Temperatures

Operating temperature range -29...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Natural rubber adhesive		
Material colour according to resistance code	4		
Number per sheet	10000		
Printing method	Thermal transfer		
Version	Self-adhesive		
Width	17 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-29 °C		
Colour	yellow		
Halogen	Yes		
Basic material	Cotton fabric		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Approval acc. to UL 969 compatible printer	No THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Device markers		
Operating temperature range	-29...80 °C		
Number per roll	10000		

Device markers

Halogen Yes

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings



