


THM GEW 20/8 GE**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

| | |
|------------|--|
| Version | THM, Device markers, 8 x 20 mm, yellow |
| Order No. | 1059880000 |
| Type | THM GEW 20/8 GE |
| GTIN (EAN) | 4032248808304 |
| Qty. | 1 items |

THM GEW 20/8 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.3 mm | Depth (inches) | 0.0118 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 20 mm | Width (inches) | 0.7874 inch |
| Net weight | 480 g | | |

Temperatures

Operating temperature range -29...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--|--|------------|--|
| Adhesive | Natural rubber adhesive | | |
| Material colour according to resistance code | 4 | | |
| Number per sheet | 10000 | | |
| Printing method | Thermal transfer | | |
| Version | Self-adhesive | | |
| Width | 20 mm | | |
| UL 94 flammability rating | V-0 | | |
| Operating temperature range, max. | 80 °C | | |
| Operating temperature range, min. | -29 °C | | |
| Colour | yellow | | |
| Halogen | Yes | | |
| Basic material | Cotton fabric | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | Label reel | |
| Approval acc. to UL 969 compatible printer | No THM MULTIMARK , THM MULTIMARK PLUS | | |
| Number of markers per combination | 1 Label reel = Device markers | | |
| Operating temperature range | -29...80 °C | | |
| Number per roll | 10000 | | |

Device markers

Halogen Yes

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings





THM GEW 20/8 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM 110/360 SW | Version | |
| Order No. | 2005070000 | Ink ribbon | |
| GTIN (EAN) | 4050118390049 | | |
| Qty. | 1 ST | | |