

**HDC KIT HE-P 06.11 M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.  
 The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.  
 Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.  
 The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

**General ordering data**

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Installation size: 3, Poles: 6, PUSH IN, 500 V, 24 A, diecast aluminium, M 20
Order No.	<a href="#">1061720000</a>
Type	HDC KIT HE-P 06.11 M
GTIN (EAN)	4032248816446
Qty.	1 items

## HDC KIT HE-P 06.11 M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Net weight 384 g

### Temperatures

Limit temperature -40 °C ... 100 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

### General data

Surface finish	Powder coating	Protection degree	IP65
Series	HE		

### Version

Size of cable entries	M 20	Number of cable entry on top	1
Number of cable entry sideways	0	Type of connection	PUSH IN
Design of locking system	End-locking clamp, lower side	Installation size	3
Sealing	NBR	Colour (RAL)	RAL 7035
BG	3		

### General data

Number of poles	6	Connection type PE	Screw connection
Installation size	3	Cable gland	M 20
Basic material	diecast aluminium	Series	HE
Rated voltage (DIN EN 61984)	500 V	Rated current (DIN EN 61984)	24 A
BG	3		

### Version

Type of connection	PUSH IN	Installation size	3
Conductor cross-section, max.	4 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Surface finish	Powder coating	Basic material	diecast aluminium
BG	3		

### Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		