

## SAIL-M12GM12G-CD-3.0B

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, Ether-CAT and Ethernet.

### General ordering data

Version	Bus line, Connecting line, M12 / M12, Number of poles: 5, 3 m, pin, straight - socket, straight, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes
Order No.	<a href="#">1060130300</a>
Type	SAIL-M12GM12G-CD-3.0B
GTIN (EAN)	4032248809059
Qty.	1 items

## SAIL-M12GM12G-CD-3.0B

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

## Dimensions and weights

Length	3 m	Length (inches)	118.1102 inch
Net weight	220 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd555bf5cb55

## Technical specifications for cable

Cable length	3 m	Sheathing colour	violet
Resistance to oils	in accordance with IEC 60811-2-1	Suitable for cable carriers	No
Core cross-section	0.34 mm <sup>2</sup>	Number of wires	5
Shielded	Yes	Halogen	Yes
Insulation	PVC	Acceleration	7 m/s <sup>2</sup>
Bending radius, min., stationary	10 x cable diameter	Bending cycles	5 Mio
Wire cross section (Print/Online)	2 x 0.34 mm <sup>2</sup> + 2 x 0.22 mm <sup>2</sup>	Resistance to spread of flame	According to IEC 60754-1
Speed	180 m/min	Sheath material	PVC
Configurable cable length	No	Outer cladding in accordance with UL AWM style	2571 (80 °C)
Hybrid cable	No	Irradiation crosslinked	No
Welding spark resistance	No	Colour coding	red, black, white, blue
Temperature range, stationary	-40...80 °C	Resistant to welding beads	No
Temperature range, moving	-25...80 °C	Number of poles	5
Outside diameter	6.7 mm ± 0.3 mm		

## General technical data

Coding	A-coded	Connection thread	M12 / M12
Contact surface	Gold-plated	LED	No
Version	pin, straight - socket, straight	Housing main material	PUR
Contact material	CuZn35PB2	Nominal voltage	125 V
Nominal current	4 A	Protection degree	IP67
Plugging cycles	≥ 100	Pollution severity	3
jumpered	No	Threaded ring material	Brass, nickel-plated
Temperature range of housing	-25...+80 °C	Tightening torque	M12: 0.8 - 1.2 Nm

**SAIL-M12GM12G-CD-3.0B**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Cable specific standards**

Poisonous gases According to EN-50267-2-1

**Electrical properties**

Nominal voltage 125 V

**General standards**

Certificate no. (cULus) E307231

**Plug, left**

Plug left M12, A-coded, Number of poles: 5, IP67, male contact, straight, plug, shielded

**Plug, right**

Plug right M12, A-coded, Number of poles: 5, IP67, female contact, straight, plug, shielded

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**SAIL-M12GM12G-CD-3.0B**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

**Dimensioned drawing**




Male, straight




Straight socket

**Pole scheme**



**Pole scheme**



**SAIL-M12GM12G-CD-3.0B**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F