

**WQB-PEN 10****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Silver grey, 57 A, Number of poles: 2, Pitch in mm (P): 10.00, Insulated: No, Width: 14.8 mm
Order No.	<a href="#">1060300000</a>
Type	WQB-PEN 10
GTIN (EAN)	4008190098346
Qty.	10 items

## WQB-PEN 10

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.0472 inch
Height	25.8 mm	Height (inches)	1.0157 inch
Width	14.8 mm	Width (inches)	0.5827 inch
Net weight	3.09 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

## Dimensions

Pitch in mm (P)	10.00 mm
-----------------	----------

## General

Number of poles	2	Installation advice	Feed-through (bushing), Direct mounting
-----------------	---	---------------------	--

## Rating data

Nominal current	57 A
-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		