

HDC KIT HE-P 24.131 M**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Installation size: 8, Poles: 24, PUSH IN, 500 V, 16 A, diecast aluminium, M 32
Order No.	1061700000
Type	HDC KIT HE-P 24.131 M
GTIN (EAN)	4032248816392
Qty.	1 items

HDC KIT HE-P 24.131 M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Net weight

813.4 g

Temperatures

Limit temperature

-40 °C ... 100 °C

Environmental Product Compliance

RoHS Compliance Status

Compliant with exemption

RoHS Exemption (if applicable/known)

6c

REACH SVHC

Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP

bfb1c983-6f18-4ba4-8907-38aad6aee076

General data

Housing main material

diecast aluminium

Protection degree

IP65

EMC housings

No

Surface finish

Powder coating

Series

HE

Material of locking element

Stainless steel, rust-proof

Version

Size of cable entries

M 32

Number of cable entry sideways

0

Number of cable entry on top

0

Design of locking system

Side-locking clamp on lower side

Type of connection

PUSH IN

Installation size

8

Sealing

NBR

BG

8

General data

Number of poles

24

Installation size

8

Basic material

diecast aluminium

Rated voltage (DIN EN 61984)

500 V

BG

8

Connection type PE

Screw connection

Cable gland

M 32

Series

HE

Rated current (DIN EN 61984)

16 A

Version

Type of connection

PUSH IN

Conductor cross-section, max.

4 mm²

Installation size

8

Conductor cross-section, min.

0.5 mm²

Surface finish

Powder coating

Basic material

diecast aluminium

BG

8

Classifications

ETIM 8.0

EC002943

ETIM 9.0

EC002943

ETIM 10.0

EC002943

ECLASS 14.0

27-44-02-92

ECLASS 15.0

27-44-02-92