

SAIL-M12GM12W-CD-1.5B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

| | |
|------------|--|
| Version | Bus line, Connecting line, M12 / M12, Number of poles: 5, 1.5 m, pin, straight - socket, 90°, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes |
| Order No. | 1062190150 |
| Type | SAIL-M12GM12W-CD-1.5B |
| GTIN (EAN) | 4032248811991 |
| Qty. | 1 items |

SAIL-M12GM12W-CD-1.5B

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

Dimensions and weights

Net weight 125 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP 1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Technical specifications for cable

| | | | |
|--|---|-------------------------------|---------------------|
| Cable length | 1.5 m | Sheathing colour | violet |
| Suitable for cable carriers | No | Shielded | Yes |
| Halogen | Yes | Insulation | PVC |
| Acceleration | 5 m/s ² | Bending radius, min., moving | 10 x cable diameter |
| Bending radius, min., stationary | 5 x cable diameter | Bending cycles | 3 Mio |
| Wire cross section (Print/Online) | 2 x 0.34 mm ² + 2 x 0.22 mm ² | Speed | 180 m/s |
| Sheath material | PVC | Configurable cable length | No |
| Outer cladding in accordance with UL AWM style | 2571 (80 °C) | Hybrid cable | No |
| Irradiation crosslinked | No | Welding spark resistance | No |
| Colour coding | white, blue, red, black | Temperature range, stationary | -40...80 °C |
| Resistant to welding beads | No | Temperature range, moving | -10...80 °C |
| Number of poles | 5 | Outside diameter | 7 mm ± 0.3 mm |

General technical data

| | | | |
|------------------------------|-----------------------------|------------------------|----------------------|
| Coding | A-coded | Connection thread | M12 / M12 |
| Contact surface | Gold-plated | LED | No |
| Version | pin, straight - socket, 90° | Housing main material | PUR |
| Contact material | Ni/Au | Nominal voltage | 125 V |
| Nominal current | 4 A | Protection degree | IP67 |
| Plugging cycles | ≥ 100 | Pollution severity | 3 |
| jumpered | No | Threaded ring material | Brass, nickel-plated |
| Temperature range of housing | -25...+80 °C | Tightening torque | M12: 0.8 - 1.2 Nm |

Electrical properties

Nominal voltage 125 V

General standards

Certificate no. (cULus) E307231

SAIL-M12GM12W-CD-1.5B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

| | |
|-----------|---|
| Plug left | M12, A-coded, IP67, male contact, straight, Plastic, shielded |
|-----------|---|

Plug, right

| | |
|------------|---|
| Plug right | M12, A-coded, IP67, female contact, angled 90°, Plastic, shielded |
|------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |

SAIL-M12GM12W-CD-1.5B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Male, straight




Socket angled

Pole scheme



Pin

Pole scheme



Socket

SAIL-M12GM12W-CD-1.5B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F