

WTA 5/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Test adapter (terminal), 0.75 mm ² , 250 V, 6 A
Order No.	1062060000
Type	WTA 5/10
GTIN (EAN)	4008190020781
Qty.	5 items

WTA 5/10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	30.3 mm	Depth (inches)	1.1929 inch
Height	17 mm	Height (inches)	0.6693 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	19.62 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	fb1756cb-1941-42d9-9a81-7624ba3e17bb		

Material data

Basic material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Number of potentials	10	Number of levels	1
----------------------	----	------------------	---

Additional technical data

With snap-in pegs	Yes	Installation advice	Direct mounting
-------------------	-----	---------------------	-----------------

Conductors for clamping (rated connection)

Connection direction	on side	Tightening torque, max.	0.3 Nm
Tightening torque, min.	0.3 Nm	Stripping length	6 mm
Type of connection	Plug-in connection	Number of connections	1
Clamping range, max.	1.5 mm ²	Clamping range, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	1 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Connection cross-section, stranded, max.	1.5 mm ²
Connection cross-section, stranded, min.	0.5 mm ²	Wire connection cross-section, solid core, max.	1 mm ²
Wire connection cross-section, solid core, min.	0.5 mm ²		

Dimensions

Pitch in mm (P)	5.00 mm	Height with TS 35	68.2 mm
-----------------	---------	-------------------	---------

WTA 5/10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General

Number of poles	10	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

Rating data

Rated cross-section	0.75 mm ²	Rated voltage	250 V
Nominal current	6 A	Volume resistance according to IEC 60947-7-x	3.56 mΩ
Power loss in accordance with IEC 60947-7-x	0.29 W		

Classifications

ETIM 8.0	EC002555	ETIM 9.0	EC002555
ETIM 10.0	EC002555	ECLASS 14.0	27-25-03-04
ECLASS 15.0	27-25-03-04		