

**WQV 70/95/2****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, Silver grey, 232 A, Number of poles: 2, Pitch in mm (P): 27.00, Insulated: No, Width: 10 mm |
| Order No.  | <a href="#">1063500000</a>   |
| Type       | WQV 70/95/2  |
| GTIN (EAN) | 4008 190028329   |
| Qty.       | 5 items  |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 61.6 mm | Depth (inches)  | 2.4252 inch |
| Height     | 37 mm   | Height (inches) | 1.4567 inch |
| Width      | 10 mm   | Width (inches)  | 0.3937 inch |
| Net weight | 101.6 g |                 |             |

### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                |               |        |             |
|----------------|---------------|--------|-------------|
| Basic material | tinned copper | Colour | Silver grey |
|----------------|---------------|--------|-------------|

### System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

### Additional technical data

|                |                 |                     |                 |
|----------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
|----------------|-----------------|---------------------|-----------------|

### Conductors for clamping (rated connection)

|                         |      |
|-------------------------|------|
| Tightening torque, max. | 3 Nm |
|-------------------------|------|

### Dimensions

|                 |          |
|-----------------|----------|
| Pitch in mm (P) | 27.00 mm |
|-----------------|----------|

### General

|                 |   |                     |                 |
|-----------------|---|---------------------|-----------------|
| Number of poles | 2 | Installation advice | Direct mounting |
|-----------------|---|---------------------|-----------------|

### Rating data

|                 |       |
|-----------------|-------|
| Nominal current | 232 A |
|-----------------|-------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |