

IE-FM5Z2VO0010MLD0LD0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, LC duplex - LC duplex, orange, Core diameter 50 µm

General ordering data

Version	Pre-assembled patch cable, crossover, LC-Duplex IP 20, LC-Duplex IP 20, 50 µm, PVC, 10 m
Order No.	1062580000
Type	IE-FM5Z2VO0010MLD0LD0X
GTIN (EAN)	4032248813261
Qty.	1 items

IE-FM5Z2V00010MLD0LD0X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	10 m	Length (inches)	393.7008 inch
Net weight	128 g		

Temperatures

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75 °C
Installation temperature	-5 °C...50 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

General standards

Connector standard	IEC 61754-20
--------------------	--------------

Standards

Connector standard	IEC 61754-20
--------------------	--------------

Fibre-optic

Fibre type	GOF, Multimode, OM2	Attenuation	≤ 2.7 dB/km at 850 nm, ≤ 0.7 dB/km at 1300 nm
Bandwidth	≥ 600 MHz*km at 850 nm, ≥ 1200 MHz*km at 1300 nm		

Cable structure

Sheath diameter	3*6 mm	Sheathing colour	orange
Standard designations	I-V(ZN)Y	Material sheath	PVC
Cable layout	ZIPCORD	Primary coating	245.00 µm
Core diameter	50 µm		

Mechanical and material properties of cable

Halogen	yes (PVC cable)	Min. bending radius, repetitive	60 mm
Min. bending radius, once only	30 mm	Resistance to spread of flame	No

Plug

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--	-----------	--

IE-FM5Z2V00010MLD0LD0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

Plug, right


Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Drawings

Detailed drawing



IE-FM5Z2V00010MLD0LD0X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

V0 material



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 5/21 MC NE WS V0	Version
Order No.	1689470001	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 ST	
Type	VT SF 6/21 MC NE WS V0	Version
Order No.	1730560001	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 ST	