

**WQV 120/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, Silver grey, 292 A, Number of poles: 3, Pitch in mm (P): 32.00, Insulated: No, Width: 10 mm |
| Order No.  | <a href="#">1063400000</a>   |
| Type       | WQV 120/3  |
| GTIN (EAN) | 4008190141363  |
| Qty.       | 5 items  |

## WQV 120/3

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 71.8 mm  | Depth (inches)  | 2.8268 inch |
| Height     | 76 mm    | Height (inches) | 2.9921 inch |
| Width      | 10 mm    | Width (inches)  | 0.3937 inch |
| Net weight | 222.34 g |                 |             |

## Temperatures

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -50 °C...55 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 100 °C         |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |             |
|---------------------------|-------|--------|-------------|
| Basic material            | PA 66 | Colour | Silver grey |
| UL 94 flammability rating | V-2   |        |             |

## System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing           | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No              |                     |                 |

## Dimensions

|                 |          |
|-----------------|----------|
| Pitch in mm (P) | 32.00 mm |
|-----------------|----------|

## General

|                 |   |                     |                 |
|-----------------|---|---------------------|-----------------|
| Number of poles | 3 | Installation advice | Direct mounting |
|-----------------|---|---------------------|-----------------|

## Rating data

|               |       |                 |       |
|---------------|-------|-----------------|-------|
| Rated voltage | 400 V | Nominal current | 292 A |
|---------------|-------|-----------------|-------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |