

**KISC M6X16-Z3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

|            |                                   |
|------------|-----------------------------------|
| Version    | SAK Series, Mounting screw, Steel |
| Order No.  | <a href="#">1063700000</a>        |
| Type       | KISC M6X16-Z3                     |
| GTIN (EAN) | 4008190120887                     |
| Qty.       | 20 items                          |

## KISC M6X16-Z3

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

|      |         |
|------|---------|
| RoHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 20 mm  | Depth (inches)  | 0.7874 inch |
| Height     | 4.8 mm | Height (inches) | 0.189 inch  |
| Width      | 4.8 mm | Width (inches)  | 0.189 inch  |
| Net weight | 6.1 g  |                 |             |

## Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                |       |                |               |
|----------------|-------|----------------|---------------|
| Basic material | Steel | Surface finish | Miscellaneous |
| Colour         | grey  |                |               |

## System specifications

|         |             |
|---------|-------------|
| Version | for busbars |
|---------|-------------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing           | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No              |                     |                 |

## Dimensions

|                                     |         |
|-------------------------------------|---------|
| Metric size of the thread, external | 6.00 mm |
|-------------------------------------|---------|

## General

|                     |                 |                |               |
|---------------------|-----------------|----------------|---------------|
| Installation advice | Direct mounting | Surface finish | Miscellaneous |
|---------------------|-----------------|----------------|---------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |