

#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com













Overvoltage coupling along the conductor path may disturb or destroy sensitive signal inputs. It is important to provide protection in the immediate vicinity of I&C devices. Weidmüller's broad product range for the I&C sector offers products in a 2-piece, pluggable design and modular terminals for tension clamp or screw connection. These products are suitable for both binary and analogue signals. Weidmüller also offers other designs with integrated components such as gas discharge tubes or varistors. VARITECTOR stands for flexible and variable surge protection by Weidmüller, tested according to product standard IEC61643-21. The VARITECTOR series can be used in applications according to IEC 61643-22 / VDE 0845-3 for classes C1, C2, C3 and D1. The VARITECTOR SPC, SSC and MCZ OVP product families optimally combine electrical and mechanical properties. Size and easy handling play an important role. This surge protection is suited for confined spaces in industrical and process automation as well as in building automation applications.

#### **General ordering data**

Version	Surge protection for instrumentation and control,
	Surge protection for measurement and control,
	UP(L/N-PE) 150 V
Order No.	<u>1063840000</u>
Туре	VSSC4 SL 24VAC/DC 0.5A
GTIN (EAN)	4032248829286
Qty.	10 items





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

Α	n	n	r	n	v	a	ls
_	v	•		v	•	u	

Approvals	( E CSAEX ÖVE)	UL)

ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (UL)	E311081

### **Dimensions and weights**

Depth	58.5 mm	Depth (inches)	2.3031 inch
Height	76.6 mm	Height (inches)	3.0157 inch
Width	6.2 mm	Width (inches)	0.2441 inch
Net weight	27.6 g		

#### **Temperatures**

Storage temperature	-40 °C80 °C	Operating temperature	-40 °C70 °C
Humidity	596 %		

### **Probability of failure**

SIL in compliance with IEC 61508	3	MTTF	2655 a
SFF	97.91 %	λges	43
PFH in 1*10-9 per hour	0.9		

### **Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	71e97bb7-979f-4330-94c0-20c629bb05e3

#### Rated data UL

Certificate No. (UL)	E311081	UL certificate	UL Zertifikat - PDF/ E311081VOL1SEC3.pdf
			(application/pdf)

### **CSA** protection data

Gas group D	IIA	Gas groups A, B	IIC	
Input-current, max. II	500 mA	Gas group C	IIB	
Internal inductance, max. LI	0 μΗ	Internal capacity, max. Cl	2 nF	
Input voltage, max. Ui	42 V			

## **General data**

Optical function display	No	Segment	Measurement - Monitoring - Setting
Version	Surge protection for measurement and control	Design	Terminal
UL 94 flammability rating	V-0	Colour	black
Protection degree	IP20	Mounting rail	TS 35
Isolating function	No		

Creation date 28.11.2025 08:01:14 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Surge voltage category	III	Pollution severity	2
Rated data IEC / EN			
Number of poles	1	Rated voltage (AC)	24 V
Rated voltage (DC)	34 V	Rated current IN	500 mA
Protection level UP (typ.)	150 V	Voltage type	AC/DC
Fuse protection	0.5 A	Volume resistance	1.8 Ω 10 %
Standards	IEC 61643-21	Lightning test current limp (10/350 μs)	1 kA
Discharge current, max. (8/20 μs)	10 kA	Requirements category acc. to IEC 61643-21	C2, C3, D1
nsertion loss	3.42 MHz	Max. continuous voltage, Uc (AC)	30 V
Max. continuous voltage, Uc (DC)	42 V	Surge current-carrying capacity D1	1 kA 10/350 μs
Surge current-carrying capacity C3	10 A 10/1000 µs	Pulse-reset capacity	≤ 35 ms
Signal transmission properties (-3 dB)	3.4 MHz	Lightning test current, limp (10/350 μs) Wire-PE	0.5 kA
Overload - failure mode	Modus 2	Discharge current In (8/20µs) wire-PE	2.5 kA
Discharge current Imax (8/20µs) wire-F		Surge current-carrying capacity C2	2.5 kA 8/20 µs 5 k\ 1.2/50 µs
Further details of approvals			
GOST certificate	GOST-Zertifikat - PDF/7950_n1-n4.pdf (application/pdf)		
Connection data			
Stripping length	10 mm	Type of connection	Screw connection
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.8 Nm
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	4 mm <sup>2</sup>
Wire cross-section, solid, min.	0.5 mm <sup>2</sup>	Wire cross-section, solid, max.	6 mm <sup>2</sup>
Conductor cross-section, flexible, AEH DIN 46228-1), min.	0.5 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	4 mm <sup>2</sup>
Connection cross-section, stranded, min	n. 0.5 mm²	Connection cross-section, stranded, max.	4 mm <sup>2</sup>
Electrical data			
Voltage type	AC/DC		
General data	1		
Number of poles	1	Protection degree	IP20
Colour	black		
Ratings IECEx/ATEX/cUL	1		1
cUL certificate	cUL Certificate - pdf/ VSSC.PDF (application/ pdf)		
Important note			
Product information		oltage-limiting part of the SPD was short-cire . The line is inoperable, but the measuring e	

Creation date 28.11.2025 08:01:14 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

4	^	١.	_	_	ifi	_	_	4:	_	_	_
ı	L _	ıa	2	SI	ITI		a	TI	n	n	s

ETIM 7.0	EC000943	ETIM 8.0	EC000943
ETIM 9.0	EC000943	ETIM 10.0	EC000943
ECLASS 12.0	27-17-15-01	ECLASS 13.0	27-17-15-01
ECLASS 14.0	27-17-15-01	ECLASS 15.0	27-17-15-01

## **Tender specification sheets**

Long specification	Surge protection in a one piece, 6.2 mm wide DIN rail module for a binary, potential-free signal circuit with 24 V UC. A signal with max. 0.5A can be protected here. When the terminal is fitted, a simultaneous electrically conducting contact is made between the mounting rail (earth) and the reference potential (ground) of the protection circuit in the terminal. Optical identification of the terminal based on the type of protected switching and the voltage level. The terminal can be labelled or marked.	Short specification	Surge protection in a one piece, 6.2 mm wide DIN rail module for a binary, potential-free signal circuit. Version: 24V UC



#### Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Drawings**



Similar to illustration



Circuit diagram

