


**IE-PI-HYB-10P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

**General ordering data**

Version	Insert, for plug insert, Hybrid
Order No.	<a href="#">1068990000</a>
Type	IE-PI-HYB-10P
GTIN (EAN)	4032248823963
Qty.	1 items

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E316369

### Dimensions and weights

Net weight	13.2 g
------------	--------

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

### General data

Wire cross-section, finely stranded, max. AWG 20 (AWG)	Wire cross-section, finely stranded, min. AWG 27 (AWG)	
Shielding	Housing main material	Nickel silver, PA 66
Insulation cross-section, max.	Insulation cross-section, min.	1 mm
Category	Wire connection cross section, finely stranded, max.	0.75 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	Protection degree	IP67 with housing
Plugging cycles	Connection 1	Hybrid (Q10)
Connection 2		

### Electrical properties

Contact resistance	≤ 5 mΩ	Volume resistance	<10 mΩ
Nominal voltage	24 V	Rated current	3 A per contact

### General standards

Certificate no. (cULus)	E316369
-------------------------	---------

### Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

### Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Drawings

Dimensioned drawing

