

VSSC4 MOV 12VDC


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Surge protection with individual components

- With suppressor diodes

Suppressor diodes work similarly as conventional Zener diodes. The diode becomes conductive within 10–100ps after a certain breakdown voltage, set by the manufacturer, is exceeded. Compared to Zener diodes, suppressor diodes have a higher current-carrying capacity and a shorter reaction time.

General ordering data

| | |
|------------|---|
| Version | Surge protection for instrumentation and control, Surge protection for measurement and control |
| Order No. | 1063950000 |
| Type | VSSC4 MOV 12VDC |
| GTIN (EAN) | 4032248829378 |
| Qty. | 10 items |

VSSC4 MOV 12VDC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UL) | E311081 |

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 58.5 mm | Depth (inches) | 2.3031 inch |
| Height | 76 mm | Height (inches) | 2.9921 inch |
| Width | 6.2 mm | Width (inches) | 0.2441 inch |
| Net weight | 27.8 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Humidity | 5...96 % | | |

Probability of failure

| | | | |
|------------------------------------|-------|------|--------|
| SIL in compliance with IEC 61508 | 3 | MTTF | 4391 a |
| SFF | 100 % | λges | 26 |
| PFH in 1*10 ⁻⁹ per hour | 0 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Rated data UL

| | | | |
|----------------------|---------|----------------|--|
| Certificate No. (UL) | E311081 | UL certificate | UL Zertifikat - PDF/ E311081VOL1SEC3.pdf (application/pdf) |
|----------------------|---------|----------------|--|

CSA protection data

| | | | |
|------------------------------|--------|----------------------------|-------|
| Gas group D | IIA | Gas groups A, B | IIC |
| Input-current, max. II | 500 mA | Gas group C | IIB |
| Internal inductance, max. LI | 0 µH | Internal capacity, max. CI | 12 nF |
| Input voltage, max. Ui | 15 V | | |

General data

| | | | |
|---------------------------|---|---------------|---------------------------------------|
| Optical function display | No | Segment | Measurement - Monitoring - Setting |
| Version | Surge protection for measurement and control | Design | Terminal |
| UL 94 flammability rating | V-0 | Colour | black |
| Protection degree | IP20 | Mounting rail | TS 35 |
| Isolating function | No | | |

VSSC4 MOV 12VDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Insulation coordination acc. to EN 50178

| | | | |
|------------------------|-----|--------------------|---|
| Surge voltage category | III | Pollution severity | 2 |
|------------------------|-----|--------------------|---|

Rated data IEC / EN

| | | | |
|--|-------------------------------------|---|---------|
| Number of poles | 1 | Rated voltage (DC) | 12 V |
| Rated current I _N | 20 A | Voltage type | AC/DC |
| Volume resistance | <0.1 Ω | Capacitance | 11.2 nF |
| Standards | IEC 61643-21 | Discharge current, max. (8/20 μs) | 1 kA |
| Requirements category acc. to IEC 61643-21 | C1 | Max. continuous voltage, U _c (DC) | 15 V |
| Surge current-carrying capacity C1 | 0.25 kA 8/20 μs 0.5 kV 1.2/50 μs | Overload - failure mode | Mode 1 |
| Rated load current I _L | 20 A | Discharge current I _{max} (8/20 μs) wire-PE1 | kA |
| Surge current-carrying capacity C2 | 1 kA 8/20 μs | | |

Further details of approvals

| | |
|------------------|--|
| GOST certificate | GOST-Zertifikat - PDF/7950_n1-n4.pdf (application/pdf) |
|------------------|--|

Connection data

| | | | |
|--|---------------------|--|-------------------|
| Stripping length | 10 mm | Type of connection | Screw connection |
| Tightening torque, min. | 0.5 Nm | Tightening torque, max. | 0.8 Nm |
| Clamping range, min. | 0.5 mm ² | Clamping range, max. | 4 mm ² |
| Wire cross-section, solid, min. | 0.5 mm ² | Wire cross-section, solid, max. | 6 mm ² |
| Conductor cross-section, flexible, AEH (DIN 46228-1), min. | 0.5 mm ² | Conductor cross-section, flexible, AEH (DIN 46228-1), max. | 4 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² | Connection cross-section, stranded, max. | 4 mm ² |

Electrical data

| | |
|--------------|-------|
| Voltage type | AC/DC |
|--------------|-------|

General data

| | | | |
|-----------------|-------|-------------------|------|
| Number of poles | 1 | Protection degree | IP20 |
| Colour | black | | |

Ratings IECEx/ATEX/cUL

| | |
|-----------------|--|
| cUL certificate | cUL Certificate - pdf/ VSSC.PDF (application/ pdf) |
|-----------------|--|

Important note

| | |
|---------------------|---|
| Product information | Mode 1: State where the voltage-limiting part of the SPD was disconnected. The voltage limiting function is no longer available, but the cable is still functional. |
|---------------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000943 | ETIM 9.0 | EC000943 |
| ETIM 10.0 | EC000943 | ECLASS 14.0 | 27-17-15-01 |
| ECLASS 15.0 | 27-17-15-01 | | |

VSSC4 MOV 12VDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Technical data

www.weidmueller.com

Tender specification sheets

Long specification

Feed-through terminal, 6.2 mm wide with varistor arrester between the signal line connection and the mounting rail potential, TS 35 contact base. A signal with max. 32A can be protected here. When the terminal is fitted, a simultaneous electrically conducting contact is made between the mounting rail (earth) and the reference potential (ground) of the protection circuit in the terminal. Optical identification of the terminal based on the type of protected switching and the voltage level. The terminal can be labelled or marked.

Short specification

Feed-through terminal with a varistor as central protection between the signal line connection and the mounting rail potential, TS 35 contact base. Version: 12 V UC

VSSC4 MOV 12VDC


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration



Circuit diagram

