


**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, yellow, 24 A, Number of poles: 3, Pitch in mm (P): 6.10, Insulated: Yes, Width: 4 mm
Order No.	<a href="#">1071600000</a>
Type	Q 3 WDL2.5S
GTIN (EAN)	4008190424923
Qty.	50 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	16.2 mm	Height (inches)	0.6378 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	2.3 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	tinned copper	Colour	yellow
----------------	---------------	--------	--------

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

### General

Number of poles	3	Installation advice	Feed-through (bushing), Direct mounting
-----------------	---	---------------------	--

### Rating data

Rated voltage	400 V	Nominal current	24 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		