

Q 4 WDL2.5S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, yellow, 24 A, Number of poles: 4, Pitch in mm (P): 6.10, Insulated: Yes, Width: 4 mm
Order No.	1071700000
Type	Q 4 WDL2.5S
GTIN (EAN)	4008190424916
Qty.	50 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	22.3 mm	Height (inches)	0.878 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	3.2 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material tinned copper Colour yellow

System specifications

Version For the terminals

Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P) 6.10 mm

General

Number of poles	4	Installation advice	Feed-through (bushing), Direct mounting
-----------------	---	---------------------	--

Rating data

Nominal current 24 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		