


VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

Overvoltage protection with individual components with varistors in terminal design
The metal-oxide varistors can be used in terminal design. They are approved for a maximum sine-wave-form power-frequency operating voltage, which is printed on the component. Any voltages greater than the permitted maximum are discharged safely within 25 ns. Varistors are used for medium to high power.

General ordering data

| | |
|------------|---|
| Version | Surge protection for instrumentation and control, Surge protection for measurement and control |
| Order No. | 1064610000 |
| Type | VSSC6 MOV 120VAC/DC |
| GTIN (EAN) | 4032248829927 |
| Qty. | 5 items |

VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



CSAEX



ROHS

Conform

UL File Number Search

[UL Website](#)

Certificate No. (UL)

E311081

Dimensions and weights

| | |
|------------|---------|
| Depth | 81 mm |
| Height | 88.5 mm |
| Width | 6.2 mm |
| Net weight | 57.8 g |

| | |
|-----------------|-------------|
| Depth (inches) | 3.189 inch |
| Height (inches) | 3.4842 inch |
| Width (inches) | 0.2441 inch |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -40 °C...80 °C |
| Humidity | 5...96 % |

| | |
|-----------------------|-------------|
| Operating temperature | -40 °C...70 |
|-----------------------|-------------|

Probability of failure

| | |
|----------------------------------|-------|
| SIL in compliance with IEC 61508 | 3 |
| SFF | 100 % |
| PFH in 1*10-9 per hour | 0 |

| | |
|------|--------|
| MTTF | 4391 a |
| λges | 26 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Rated data UL

| | | | |
|----------------------|---------|----------------|---|
| Certificate No. (UL) | E311081 | UL certificate | UL Zertifikat - PDF / E311081VOL1SEC3.pdf (application/pdf) |
|----------------------|---------|----------------|---|

CSA protection data

| | |
|------------------------------|-------|
| Gas group D | IIA |
| Input-current, max. II | 12 A |
| Internal inductance, max. LI | 0 µH |
| Input voltage, max. Ui | 212 V |

| | |
|----------------------------|------|
| Gas groups A, B | IIC |
| Gas group C | IIB |
| Internal capacity, max. CI | 2 nF |

General data

| | | | |
|---------------------------|--|---------------|------------------------------------|
| Optical function display | No | Segment | Measurement - Monitoring - Setting |
| Version | Surge protection for measurement and control | Design | Terminal |
| UL 94 flammability rating | V-0 | Colour | black |
| Protection degree | IP20 | Mounting rail | TS 35 |
| Isolating function | No | | |

VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Insulation coordination acc. to EN 50178

| | | | |
|------------------------|-----|--------------------|---|
| Surge voltage category | III | Pollution severity | 2 |
|------------------------|-----|--------------------|---|

Rated data IEC / EN

| | | | |
|---------------------------------------|----------------|---|----------------------------------|
| Number of poles | 1 | Rated voltage (AC) | 120 V |
| Rated voltage (DC) | 170 V | Rated current IN | 12 A |
| Voltage type | AC/DC | Volume resistance | <0.1 Ω |
| Capacitance | 283 pF | Standards | According to IEC61643-21 |
| Discharge current, max. (8/20 µs) | 12 kA | Requirements category acc. to IEC 61643-21 | C1, C2 |
| Insertion loss | ≤ 0.5 dB | Max. continuous voltage, Uc (AC) | 150 V |
| Max. continuous voltage, Uc (DC) | 212 V | Surge current-carrying capacity C1 | 0.5 kA 8/20 µs 1 kV 1.2/50 µs |
| Overload - failure mode | Mode 1 | Rated load current IL | 12 A |
| Discharge current In (8/20µs) wire-PE | 0.5 kA | Discharge current Imax (8/20µs) wire-PE6 kA | |
| Surge current-carrying capacity C2 | 1.5 kA 8/20 µs | | |

Further details of approvals

| | |
|------------------|--|
| GOST certificate | GOST-Zertifikat - PDF/7950_n1-n4.pdf (application/pdf) |
|------------------|--|

Connection data

| | | | |
|--|---------------------|--|-------------------|
| Stripping length | 10 mm | Type of connection | Screw connection |
| Tightening torque, min. | 0.5 Nm | Tightening torque, max. | 0.8 Nm |
| Clamping range, min. | 0.5 mm ² | Clamping range, max. | 4 mm ² |
| Wire cross-section, solid, min. | 0.5 mm ² | Wire cross-section, solid, max. | 6 mm ² |
| Conductor cross-section, flexible, AEH (DIN 46228-1), min. | 0.5 mm ² | Conductor cross-section, flexible, AEH (DIN 46228-1), max. | 4 mm ² |
| Connection cross-section, stranded, min. 0.5 mm ² | | Connection cross-section, stranded, max. | 4 mm ² |

Electrical data

| | |
|--------------|-------|
| Voltage type | AC/DC |
|--------------|-------|

General data

| | | | |
|-----------------|-------|-------------------|------|
| Number of poles | 1 | Protection degree | IP20 |
| Colour | black | | |

Important note

| | |
|---------------------|---|
| Product information | Mode 1: State where the voltage-limiting part of the SPD was disconnected. The voltage limiting function is no longer available, but the cable is still functional. |
|---------------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000943 | ETIM 9.0 | EC000943 |
| ETIM 10.0 | EC000943 | ECLASS 14.0 | 27-17-15-01 |
| ECLASS 15.0 | 27-17-15-01 | | |

VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Technical data**Tender specification sheets**

| | | | |
|--------------------|---|---------------------|--|
| Long specification | Feed-through terminal, 6.2mm wide with varistors between the two signal lines and the mounting rail potential, TS 35 contact base. A signal with max. 12A can be protected here. When the terminal is fitted, a simultaneous electrically conducting contact is made between the mounting rail (earth) and the reference potential (ground) of the protection circuit in the terminal. Optical identification of the terminal based on the type of protected switching and the voltage level. The terminal can be labelled or marked. | Short specification | Feed-through terminal with varistors (MOV) between two signal lines and the mounting rail potential, TS 35 contact base. Version: 120 V UC |
|--------------------|---|---------------------|--|


VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Similar to illustration



Circuit diagram



VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Accessories**Accessories (end plates)**

End plates (AP) for the VSSC product series in light blue and black

General ordering data

| | | |
|------------|----------------------------|-----------------|
| Type | AP VSSC6 | Version |
| Order No. | 1063110000 | VSSC, End plate |
| GTIN (EAN) | 4032248947553 | |
| Qty. | 50 ST | |

Blank

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/5 MC NE WS | Version |
| Order No. | 1609801044 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111 | Weidmueller, white |
| Qty. | 1000 ST | |

SnapMark

SnapMark - this tag carrier has been developed specifically for the I-series double-level terminal IDK 1.5N. The flexible pivot mechanism allows cross-connections to be easily installed or removed. It can hold four DEK 5 labelling tags or two WS 10/5 Middle connector markers.

VSSC6 MOV 120VAC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**General ordering data**

| | | |
|------------|----------------------------|--|
| Type | SNAPMARK I | Version |
| Order No. | 1805880000 | Group markers, Terminal marker, 23 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4032248273614 | Weidmüller, white |
| Qty. | 50 ST | |