

## WQL 3 WFF120

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 3
Order No.	<a href="#">1065600000</a>
Type	WQL 3 WFF120
GTIN (EAN)	4008 19002 164 1
Qty.	5 items

## WQL 3 WFF120

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	119 mm	Height (inches)	4.685 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	115.6 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Copper - zinc	Colour	grey
----------------	---------------	--------	------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

## Dimensions

Pitch in mm (P)	42.00 mm
-----------------	----------

## General

Number of poles	3	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Nominal current	269 A
-----------------	-------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		