

SM 27/18 K MC NE GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|----------------------------------------------|
| Version | SwitchMark, Device markers, 18 x 27 mm, grey |
| Order No. | 1073340000 |
| Type | SM 27/18 K MC NE GR |
| GTIN (EAN) | 4032248831425 |
| Qty. | 80 items |

SM 27/18 K MC NE GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 18 mm | Height (inches) | 0.7087 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 1.31 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.008 kg CO2 eq. | |

General data

| | | | |
|----------------------------------------------|---------------------------------------------------------------------------------------------|-----------|--|
| Adhesive | Double-sided adhesive tape | | |
| Material colour according to resistance code | 8 | | |
| Version | Self-adhesive | | |
| Width | 27 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 60 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | grey | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Device markers | | |
| Operating temperature range | -40...60 °C | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

