

KDSW M32 BN L NI 1 G32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



The KDSW features a special ring in the shape of a truncated cone. The ring enables connections between cable and lines with single-wire armouring and lead-sheath armouring. This ensures a conductive connection between the cable and the cable gland. In addition, the KDSW comes with two seals which provide sealing for the outer and inner parts of the cable insulation. The cable armouring is located between the inner and outer insulation. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -35°C to +90°C. When using a silicone seal, a temperature range of -60°C to +180°C is possible. When both sealing materials are used, it is possible to achieve IP66 or IP67 protection. The KDSW is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e.

General ordering data

Version	KDSW (Klippon double seal SWA Ex cable gland), Cable glands, straight, M 32, 16 mm, Single-wire armouring, Lead sheath armouring, 1.6 - 2 mm, OD min. 23.2 - OD max. 30.5 mm, ID min. 19.00 - ID max. 26.30 mm, IP66, IP68 - 2.5 bar, Brass, nickel-plated
Order No.	1074850000
Type	KDSW M32 BN L NI 1 G32
GTIN (EAN)	4032248837205
Qty.	10 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KDSW M32 BN L NI 1 G32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals	IECEXSIR; SIRAATEX
Approvals	EAC; ATEX; IECEX
Approvals	



ROHS	Conform
------	---------

Dimensions and weights

Height	65 mm	Height (inches)	2.5591 inch
Length	65 mm	Length (inches)	2.5591 inch
Net weight	420 g		

Temperatures

Operating temperature	-35 °C...90 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	3394d55b-7892-488f-8603-ea218c1d0691

Certificate numbers cable gland

Identification	ATEX: II 2G, Ex db IIC Gb, Ex eb IIC Gb, II 1D, Ex ta IIIC Da, IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (IECEX)	IECEX CML 19.0109X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate No. (ATEX)	SIRA05ATEX 1286X
Approval conditions	ATEX, IECEX		

General information

Outer cable diameter, max.	30.5 mm	Outer cable diameter, min.	23.2 mm
Inner cable diameter, max.	26.30 mm	Inner cable diameter, min.	19.00 mm
Protection degree with GWDR	IP66, IP68 - 2.5 bar	Armour, max.	2 mm
Armour, min.	1.6 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-35 °C	Pitch of thread	1.5 mm
Halogen	Yes	AF size 1	46 mm
AF size 2	46 mm	Protection degree	IP54
Cable gland	metric, nickel-plated brass	Basic material	Brass, nickel-plated
Seal insert	CR	Sealing	CR
External thread	M 32	Length of thread	16 mm
Water depth	25 m (30 Min.)	Type of armouring, short term	SWA
Explosion protection type	Improved safety Ex e, Pressure-resistant Ex d encapsulation	Type of armouring	Single-wire armouring, Lead sheath armouring
Installation guidelines	See assembly instructions	Size of protective cap	L46

KDSW M32 BN L NI 1 G32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		

KDSW M32 BN L NI 1 G32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M32 MS	Version	
Order No.	1737020000	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated	
GTIN (EAN)	4008190956493		
Qty.	100 ST		

Safety serrated washer



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SZS M32	Version	
Order No.	1736330000	SZS (serrated washer), Retaining toothed washers, M 32, Stainless steel 1.4404 (316L)	
GTIN (EAN)	4008190963538		
Qty.	10 ST		

Earth tags



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	EA-RING MS/M 32	Version	
Order No.	1736510000	EA (earthing rings), Earthing ring, Miscellaneous, M 32, Brass, nickel-plated	
GTIN (EAN)	4008190963613		
Qty.	20 ST		

KDSW M32 BN L NI 1 G32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M32	Version	
Order No.	1076650000	KSWN (flat gasket - nylon), Sealing ring, M 32, Nylon 6	
GTIN (EAN)	4032248838691		
Qty.	25 ST		

Protective caps



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSP L46	Version	
Order No.	1736600000	KSP (Klippon shroud), Protective cap, PVC	
GTIN (EAN)	4008190956257		
Qty.	10 ST		
Type	KSP L46 S	Version	
Order No.	0930700004	KSP (Klippon shroud), Protective cap, Silicone	
GTIN (EAN)	4032248975990		
Qty.	10 ST		