

FBC PA M12 MA-FMA 2M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

Version	Bus line, Connecting line, M12 / M12, Number of poles: 2, 2 m, pin, 90°; - socket 90°; Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes
Order No.	1076550200
Type	FBC PA M12 MA-FMA 2M
GTIN (EAN)	4032248834174
Qty.	1 items
Delivery status	Discontinued
Available until	2025-11-29T00:00:00+01:00

FBC PA M12 MA-FMA 2M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 187 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP 273a2adc-147a-4b75-9d50-227deee55a05

Technical specifications for cable

Cable length	2 m	Sheathing colour	black
Suitable for cable carriers	No	Core cross-section	1 mm ²
Shielded	Yes	Halogen	Yes
Insulation	PE	Bending radius, min., moving	8 x cable diameter
Bending radius, min., stationary	8 x cable diameter	Sheath material	PVC
Configurable cable length	No	Hybrid cable	No
Irradiation crosslinked	No	Welding spark resistance	No
Colour coding	red, green	Temperature range, stationary	-30...80 °C
Resistant to welding beads	No	Temperature range, moving	-5...60 °C
Number of poles	2	Outside diameter	8 mm ± 0.4 mm

General technical data

Coding	A-coded	Connection thread	M12 / M12
Contact surface	Gold-plated	LED	No
Version	pin, 90°; - socket 90°;	Housing main material	PUR
Insulation resistance	108 Ω	Contact material	Ni/Au
Nominal voltage	100 V	Protection degree	IP67
Plugging cycles	≥ 100	Pollution severity	3
jumpered	No	Threaded ring material	Brass, nickel-plated
Temperature range of housing	-25...+80 °C	Tightening torque	M12: 0.8 - 1.2 Nm

Electrical properties

Insulation resistance	108 Ω	Nominal voltage	100 V
-----------------------	-------	-----------------	-------

Plug, left

Plug left M12, A-coded, IP67, male contact, angled 90°, Plastic, shielded

FBC PA M12 MA-FMA 2M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, right**

Plug right	M12, A-coded, IP67, female contact, angled 90°, Plastic, shielded
------------	---

Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

FBC PA M12 MA-FMA 2M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing




Male, angled




Socket angled

Pole scheme



Pin

Pole scheme



Socket

Drawings

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F