

## SAIE-M8S-4-0.5U-FP-M8

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

### General ordering data

Version	Built-in plugs, M8 thread, pin, straight, Mounting thread: M8, Number of poles: 4, Strand / cable length: 0.5 m
Order No.	<a href="#">1078720000</a>
Type	SAIE-M8S-4-0.5U-FP-M8
GTIN (EAN)	4032248840618
Qty.	1 items

## SAIE-M8S-4-0.5U-FP-M8

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Net weight 12 g

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

## Technical specifications for cable

Core cross-section	0.25 mm <sup>2</sup>	Strand / cable length	0.5 m
Colour coding	brown, white, blue, black	Number of poles	4

## Technical data customisable plug-in connectors

Number of poles	4	Coding	none
Contact surface	Gold-plated	Type of connection	Pin
Housing main material	Brass, nickel-plated	Nominal voltage	30 V
Nominal current	4 A	Protection degree	IP67, when screwed in
Plugging cycles	≥ 100	Cable gland	M 8
Temperature range of housing	-30...+90 °C		

## Standards

Connector standard IEC 61076-2-104

## General data

Number of poles	4	Coding	none
Connection thread	M8 thread	Contact surface	Gold-plated
Core cross-section	0.25 mm <sup>2</sup>	Type of connection	Pin
Housing main material	Brass, nickel-plated	Nominal voltage	30 V
Nominal current	4 A	Protection degree	IP67, when screwed in
Plugging cycles	≥ 100	Cable gland	M 8
Basic material	PVC	Rated voltage	60 V (3-pole) / 30 V (4-pole)
Connection 1	M8	Connection 2	Flying wires
Strand / cable length	0.5 m	Mounting thread	M8
Temperature range of housing	-30...+90 °C	Conductor O.D.	-

## Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		


SAIE-M8S-4-0.5U-FP-M8

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


www.weidmueller.com

Drawings

Wiring diagram



Pole scheme



Installation cut-out

