


**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cross-connector (terminal), when screwed in, yellow, 24 A, Number of poles: 3, Pitch in mm (P): 6.10, Insulated: Yes, Width: 4 mm |
| Order No.  | <a href="#">1071600000</a>  |
| Type       | Q 3 WDL2.5S   |
| GTIN (EAN) | 4008190424923   |
| Qty.       | 50 items  |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 9.5 mm  | Depth (inches)  | 0.374 inch  |
| Height     | 16.2 mm | Height (inches) | 0.6378 inch |
| Width      | 4 mm    | Width (inches)  | 0.1575 inch |
| Net weight | 2.3 g   |                 |             |

### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                |               |        |        |
|----------------|---------------|--------|--------|
| Basic material | tinned copper | Colour | yellow |
|----------------|---------------|--------|--------|

### System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

### Additional technical data

|                          |                 |                     |  |
|--------------------------|-----------------|---------------------|--|
| Type of fixing           | when screwed in | Installation advice | Feed-through (bushing),<br>Direct mounting |
| Explosion-tested version | No              |                     |  |

### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 6.10 mm |
|-----------------|---------|

### General

|                 |   |                     |  |
|-----------------|---|---------------------|--|
| Number of poles | 3 | Installation advice | Feed-through (bushing),<br>Direct mounting |
|-----------------|---|---------------------|--|

### Rating data

|                 |      |
|-----------------|------|
| Nominal current | 24 A |
|-----------------|------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |