

WQB PEN 35N



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| Version | Cross-connector (terminal), when screwed in, Silver grey, 125 A, Number of poles: 2, Pitch in mm (P): 16.00, Insulated: No, Width: 24.6 mm | |
|------------|--|--|
| Order No. | <u>1079500000</u> | |
| Туре | WQB PEN 35N | |
| GTIN (EAN) | 4008190370121 | |
| Qty. | 10 items | |



WQB PEN 35N



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Approvals | | | | |
|---------------------------|-----------------------------|--------------------------|-------------|--|
| ROHS | Conform | | | |
| | Conform | | | |
| Dimensions and weights | | | <u> </u> | |
| Depth | 2 mm | Depth (inches) | 0.0787 inch | |
| Height | 25.9 mm | Height (inches) | 1.0197 inch | |
| Width | 24.6 mm | Width (inches) | 0.9685 inch | |
| Net weight | 11.6 g | | | |
| Temperatures | | | | |
| Storage temperature | -25 °C55 °C | Ambient temperature | -5 °C40 °C | |
| Environmental Product Con | npliance | | | |
| 2 110 0 | | | | |
| RoHS Compliance Status | Compliant without exemption | | | |
| REACH SVHC | No SVHC above 0.1 wt | % | | |
| Material data | | | | |
| Basic material | tinned copper | Colour | Silver grey | |
| System specifications | | | | |
| Version | Cross-connector | | , | |
| Additional technical data | | | | |
| | | | · | |
| Type of fixing | when screwed in | Explosion-tested version | No | |
| Type of mounting | when screwed in | | | |
| Dimensions | | | , | |
| Pitch in mm (P) | 16.00 mm | | | |
| General | | | | |
| Number of poles | 2 | | , | |
| Rating data | | | | |
| | | | | |
| Nominal current | 125 A | | | |
| Classifications | | | | |
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 | |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 | |
| ETIM 10.0 | EC000489 | ECLASS 9.0 | 27-14-11-40 | |
| ECLASS 9.1 | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 | |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 | |
| ECLASS 13.0 | 27-25-03-03 | ECLASS 14.0 | 27-25-03-03 | |
| 202 100 1010 | _, _, ., ., | 202.00 | | |

Creation date 28.11.2025 10:08:52 MEZ

Catalogue status / Drawings 2