


**HDC HP 250 F 25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	HDC insert, Female, Crimp connection, Installation size: 250
Order No.	<a href="#">1079720000</a>
Type	HDC HP 250 F 25
GTIN (EAN)	4032248841646
Qty.	1 items

## HDC HP 250 F 25

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Length	83.2 mm	Length (inches)	3.2756 inch
Diameter	32 mm	Net weight	81.37 g

## Temperatures

Limit temperature	-50 °C ... 120 °C
-------------------	-------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

## General data

Plugging cycles, silver	≥ 500	Type of connection	Crimp connection
Installation size	250	UL 94 flammability rating	V-0
Volume resistance	≤0.1 mΩ	Colour	black
Insulation resistance	1010 Ω	Insulating material	PA GF
Conductor cross-section	25 mm <sup>2</sup>	Surface finish	Silver passivated
Plugging cycles	≥ 500	Type	Female
Pollution severity	PD 2 (PD 3)	Basic material	Copper alloy
Series	HighPower	Rated impulse voltage (DIN EN 61984)	15 kV
Operating voltage, max. (total temperature=60°C)	2300 V	Free from halogens	false
Rated current acc. to DIN EN 61984 (ambient temperature=20°C)	140 A	BG	250

## Connection data PE

Connection type PE	Crimp connection, Screw connection
--------------------	------------------------------------

## Power contact

Type of connection, power contact	Crimp connection	Stripping length, performance contact	24 mm
Rated impulse voltage (DIN EN 61984), power contact	15 kV		

## Version

Stripping length, rated connection	24 mm	Type of connection	Crimp connection
Installation size	250	Volume resistance	≤0.1 mΩ
Conductor cross-section, max.	25 mm <sup>2</sup>	Conductor cross-section, min.	25 mm <sup>2</sup>
Surface finish	Silver passivated	Basic material	Copper alloy
BG	250		

## Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do
---------------------	--

## Technical data

not exceed the rated voltage. For applications outside of this specification, please contact us. The rated voltage of 3.0 kV must be reduced by 20% at operating temperatures above 110°C.

### Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC HP 250 F 25

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

Drawings

www.weidmueller.com

