HDC IP68 06B AS



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com









The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP66, IP68, in plugged condition, Bulkhead housing, Clamping yoke connection, Standard
Order No.	<u>1081510000</u>
Туре	HDC IP68 06B AS
GTIN (EAN)	4032248844258
Qty.	1 items



HDC IP68 06B AS



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approva	als
---------	-----

Approvals



ROHS Conform

Dimensions and weights

Height	30 mm	Height (inches)	1.1811 inch
Width	58 mm	Width (inches)	2.2835 inch
Mounting dimension - height	32 mm	Mounting dimension - width	70 mm
Net weight	141.68 g		

Temperatures

Limit temperature -50 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Chemical resistance	Substance	Acetone	
	Chemical resistance	Resistant	
	Substance	Diesel oil	
	Chemical resistance	Unstable	
	Substance	Ethyl alcohol	
	Chemical resistance	Resistant	
	Substance	Transmission oil	
	Chemical resistance	Conditionally resistant	
	Substance	Hydraulic oil	
	Chemical resistance	Conditionally resistant	
	Substance	Petroleum benzine	
	Chemical resistance	Unstable	
	Substance	Sweat	
	Chemical resistance	Conditionally resistant	
	Substance	Premium gasoline	
	Chemical resistance	Unstable	
	Substance	Water	
	Chemical resistance	Resistant	
	Substance	UV	
	Chemical resistance	Resistant	
	Substance	Ozone	
	Chemical resistance	Resistant	

Dimensions

Hole pitch length A2	70 mm	Cable entry	w. thread
Total length housing	132 mm	Height of housing B	30 mm

General data

Housing main material	diecast aluminium	Surface finish	Powder coating
Protection degree	IP66, IP68, in plugged condition	EMC housings	Yes

Creation date 28.11.2025 12:09:12 MEZ

Catalogue status / Drawings 2



HDC IP68 06B AS



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Top part/bottom part/lid	lower part	Design of housing	Bulkhead housing
Design of locking system	Clamping yoke connection	Design	Standard
Installation size	3	Cable entry	w. thread
Туре	Bulkhead (feed-through)	Clamp version	Clamping yoke connection
Sealing	Silicone	Colour (RAL)	RAL 9011, RAL 9005
BG	3	Suitable for ModuPlug®	Yes

Important note

Version

Product information	When mounting the housings, make sure that the flat gasket is correctly seated.

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

Catalogue status / Drawings

Data sheet

HDC IP68 06B AS



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings

