

KUB M40 BS O NI 2 G40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The KUB features a special ring in the shape of a truncated cone. The ring enables connections between single-wire-armoured and metal-foil-armoured cables and braided-armoured lines. This ensures a conductive connection between the cable and the cable gland. It is also possible to connect non-armoured cables and lines. The KUB also features a seal for sealing the outer cable insulation. The area of the connecting cable that is exposed after stripping the inner insulation is then encapsulated with the encapsulation compound (included in delivery). Thus all of the gaps and spaces between the individual wire strands are 100% sealed. The cable gland is certified for use in temperatures ranging from -60°C to +135°C. The O-ring and the encapsulation compound are both included in the delivery. When encapsulated, the cable gland guarantees IP66 or IP68 protection at a depth of 100 metres under water (a pressure of 10 bar for 7 days). The KUB is only approved for use with pressure-resistant Ex d encapsulation. This type of cable gland must be used in the following cases: 1.) If the surroundings of an IIC device require it or when the enclosure contains components that could trigger an internal explosion (such as a flying spark) 2.) When the surroundings of no group-IIC devices require it, the enclosure contains components that could trigger an internal explosion, it is a Zone-1 installation, and the enclosure volume is greater than 2 dm³.

General ordering data

Version	KUB (Klippon universal die-cast Ex cable gland), Cable glands, straight, M 40, 16 mm, Single-wire armouring, Metal foil armouring, Braided armouring, 0.1 - 2 mm, OD min. 33 - OD max. 40.6 mm, ID min. 29.00 - ID max. 32.20 mm, IP68 - 10 bar, Brass, nickel-plated
Order No.	1095210000
Type	KUB M40 BS O NI 2 G40
GTIN (EAN)	4032248868223
Qty.	10 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KUB M40 BS O NI 2 G40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals	IECEXSIR; SIRAATEX
Approvals	EAC; ATEX; IECEX
Approvals	



ROHS	Conform
------	---------

Dimensions and weights

Height	105 mm	Height (inches)	4.1338 inch
Length	105 mm	Length (inches)	4.1338 inch
Net weight	1060 g		

Temperatures

Operating temperature	-60 °C... 135 °C
-----------------------	------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	3394d55b-7892-488f-8603-ea218c1d0691

Certificate numbers cable gland

Identification	ATEX: II 2 GD, Ex d IIC Gb, Ex e IIC Gb, Ex tb IIIC (Ta = -60°C to + 135°C) or II 1D, Ex ta IIIC Da (Ta = -60°C to + 135°C), IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (IECEX)	IECEX CML 19.0109X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate No. (ATEX)	SIRA05ATEX1288X
Approval conditions	ATEX, IECEX		

General information

Outer cable diameter, max.	40.6 mm	Outer cable diameter, min.	33 mm
Inner cable diameter, max.	32.20 mm	Inner cable diameter, min.	29.00 mm
O-Ring	Silicone	Protection degree with GWDR	IP68 - 10 bar
Number of wires	130	Armour, max.	2 mm
Armour, min.	0.1 mm	Operating temperature range, max.	135 °C
Operating temperature range, min.	-60 °C	Pitch of thread	1.5 mm
Halogen	No	AF size 1	55 mm
AF size 2	55 mm	Protection degree	IP68 - 10 bar
Cable gland	metric, nickel-plated brass	Basic material	Brass, nickel-plated
Seal insert	Silicone	Sealing	Silicone
External thread	M 40	Length of thread	16 mm
Water depth	100 m (30 Min.)	Type of armouring, short term	SWA, STA, SWB
Encapsulation compound	Processing temperature at 21°C, the sealing compound is hardened after one hour, After 4 hours, the cable gland	Explosion protection type	Pressure-resistant Ex d encapsulation

KUB M40 BS O NI 2 G40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

	can be installed and initial commissioning can take place		
Type of armouring	Single-wire armouring, Metal foil armouring, Braided armouring	Max. diameter of bundled wires	28.80
Installation guidelines	See assembly instructions	Size of protective cap	EL55

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		

KUB M40 BS O NI 2 G40
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Accessories
Brass lock nuts, nickel-plated


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M40 MS	Version
Order No.	1737030000	SKMU MS (brass locknut), Locknut, M 40, 5 mm, Brass, nickel-plated
GTIN (EAN)	4008190956509	
Qty.	50 ST	

Safety serrated washer


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SZS M40	Version
Order No.	1736340000	SZS (serrated washer), Retaining toothed washers, M 40, Stainless steel 1.4404 (316L)
GTIN (EAN)	4008190963545	
Qty.	5 ST	

Earth tags


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	EA-RING MS/M 40	Version
Order No.	1736520000	EA (earthing rings), Earthing ring, Miscellaneous, M 40, Brass, nickel-plated
GTIN (EAN)	4008190963637	
Qty.	10 ST	

KUB M40 BS O NI 2 G40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Vulcanised fibre gasket - KSWF



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWF M40	Version
Order No.	1076710000	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 40, Vulcanized
GTIN (EAN)	4032248838639	fibre
Qty.	25 ST	

Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M40	Version
Order No.	0899780000	KSWN (flat gasket - nylon), Sealing ring, M 40, Nylon 6
GTIN (EAN)	4032248850150	
Qty.	25 ST	

Protective caps



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSP EL55	Version
Order No.	1076760000	KSP (Klippon shroud), Protective cap, PVC
GTIN (EAN)	4032248838578	
Qty.	10 ST	