


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**



























Power on board - 100% safety, 100% integration, 100% cost-effectiveness:

The compact, efficient solution for UL-600V applications in the lower performance range up to 12kVA.

- 29 A at 630 V (IEC)
- 20 A at 600 V (UL)
- Single compartment mating profile
- Clamping range: 0.08 4 mm<sup>2</sup> / AWG 28 12

Assistance with device approval:

- meets the requirements for 600 V in accordance with UL508/UL840
- meets the more stringent touch-safety requirements of IEC68100-5-1

The slimming cure for multiple-stage device series: reduced size and cut costs in the high-volume lower performance range without compromising device approval!

## **General ordering data**

Version	PCB plug-in connector, female plug, 7.62 mm, Number of poles: 10, 180°, Clamping yoke con- nection, Clamping range, max. : 4 mm², Box
Order No.	<u>1095870000</u>
Туре	BLZ 7.62HP/10/180F SN OR BX
GTIN (EAN)	4032248868704
Qty.	15 items
Product data	IEC: 630 V / 29 A / 0.2 - 4 mm <sup>2</sup> UL: 600 V / 20 A / AWG 28 - AWG 12
Packaging	Вох





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Approvals	Αı	pp	ro	va	Is
-----------	----	----	----	----	----

Approvals	c <b>FL</b> *us
ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	E60693

## **Dimensions and weights**

Depth	23.3 mm	Depth (inches)	0.9173 inch
Height	18.3 mm	Height (inches)	0.7205 inch
Width	85.28 mm	Width (inches)	3.3575 inch
Net weight	21 g		

## **Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.422 kg CO2eq.

#### **System Parameters**

OMNIMATE Power - series BL/SL 7.62HP	Type of connection	Field connection
Clamping yoke connection	Pitch in mm (P)	7.62 mm
0.300 "	Conductor outlet direction	180°
10	L1 in mm	68.58 mm
2.700 "	Number of rows	1
1	Rated cross-section	2.5 mm <sup>2</sup>
Safe from finger touch	Touch-safe protection acc. to DIN VDE 0470	IP 20
IP20	Volume resistance	5.00 mΩ
Yes	Stripping length	7 mm
0.15 Nm	Tightening torque for screw flange, max.	0.25 Nm
0.4 Nm	Tightening torque, max.	0.5 Nm
M 2.5	Screwdriver blade	0.6 x 3.5
DIN 5264	Plugging cycles	25
9.5 N	Pulling force/pole, max.	8.5 N
	BL/SL 7.62HP  Clamping yoke connection 0.300 " 10 2.700 " 1 Safe from finger touch  IP20 Yes 0.15 Nm 0.4 Nm M 2.5 DIN 5264	BL/SL 7.62HP

### **Material data**

Insulating material	PBT	Colour	orange
Colour chart (similar)	RAL 2000	Insulating material group	Illa
Comparative Tracking Index (CTI)	≥ 200	Insulation resistance	≥ 108 Ω
Moisture Level (MSL)		UL 94 flammability rating	V-0
Contact material	Cu-alloy	Contact surface	tinned
Layer structure of plug contact	48 µm Sn hot-dip tinned	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	100 °C		

#### **Conductors suitable for connection**

Clamping range, min.	0.08 mm <sup>2</sup>	
Clamping range, max.	4 mm <sup>2</sup>	

Creation date 28.11.2025 04:59:52 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Wire connection cross section AWG,	AWG 28	
min.		
Wire connection cross section AWG, max.	AWG 12	
Solid, min. H05(07) V-U	0.2 mm <sup>2</sup>	
Solid, max. H05(07) V-U	4 mm²	
Flexible, min. H05(07) V-K	0.2 mm <sup>2</sup>	
Flexible, max. H05(07) V-K	4 mm <sup>2</sup>	
w. plastic collar ferrule, DIN 46228 pt		
min.		
w. plastic collar ferrule, DIN 46228 pt max.	4, 2.5 mm²	
w. wire end ferrule, DIN 46228 pt 1, min.	0.2 mm <sup>2</sup>	
w. wire end ferrule, DIN 46228 pt 1, max.	2.5 mm <sup>2</sup>	
Plug gauge in accordance with EN 60999 a x b; ø	2.8 mm x 2.4 mm	
Clampable conductor	Cross-section for conductor connection	Type fine-wired
		nominal 0.25 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 10 mm
		Recommended wire- H0,25/12 HBL end ferrule
	Cross-section for conductor connection	Type fine-wired
	Greek Greek For Schwarter Grimsenen	nominal 0.34 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 10 mm
		Recommended wire- H0,34/12 TK
		end ferrule
	Cross-section for conductor connection	Type fine-wired
		nominal 0.5 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 6 mm
		Recommended wire- H0.5/6 end ferrule
	Cross-section for conductor connection	Type fine-wired
	Greek seemen for semanation seminosium.	nominal 0.75 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 6 mm
	This one is a	Recommended wire- end ferrule
	Cross-section for conductor connection	Type fine-wired
	Greek seemen for semanation seminosium.	nominal 1 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 6 mm
	Wile sha ishale	Recommended wire- end ferrule
	Cross-section for conductor connection	Type fine-wired
	Closs-section for conductor connection	nominal 1.5 mm <sup>2</sup>
	wire end ferrule	
	wile ellu lellule	Stripping length nominal 7 mm  Recommended wire- H1,5/7
		end ferrule
	Cross-section for conductor connection	Type fine-wired
		nominal 2.5 mm <sup>2</sup>
	wire end ferrule	Stripping length nominal 7 mm
		Recommended wire- H2,5/7 end ferrule
Reference text	The outside diameter of the plastic collar should be chosen depending on the product and	uld not be larger than the pitch (P), Length of ferrules d the rated voltage.

Creation date 28.11.2025 04:59:52 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Rated data acc. to IEC			
tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	29 A
Rated current, max. number of poles (Tu=20°C)	26.5 A	Rated current, min. number of poles (Tu=40°C)	25 A
Rated current, max. number of poles (Tu=40°C)	23 A	Rated voltage for surge voltage class / pollution degree II/2	630 V
Rated voltage for surge voltage class / pollution degree III/2	500 V	Rated voltage for surge voltage class / pollution degree III/3	400 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	6 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	6 kV	Short-time withstand current resistance	3 x 1s with 180 A
Creepage distance, min.	11.3 mm	Clearance, min.	9.8 mm

## Rated data acc. to CSA

Rated voltage (Use group B / CSA)	600 V	Rated voltage (Use group C / CSA)	600 V
Rated voltage (Use group D / CSA)	600 V	Rated current (Use group B / CSA)	20 A
Rated current (Use group C / CSA)	20 A	Rated current (Use group D / CSA)	5 A
Wire cross-section, AWG, min.	AWG 28	Wire cross-section, AWG, max.	AWG 12

## Rated data acc. to UL 1059

Institute (cURus)	CURUS	Certificate No. (cURus)	E60693
Rated voltage (Use group B / UL 1059)	600 V	Rated voltage (Use group C / UL 1059)	600 V
Rated voltage (Use group D / UL 1059)	600 V	Rated current (Use group B / UL 1059)	20 A
Rated current (Use group C / UL 1059)	20 A	Rated current (Use group D / UL 1059)	5 A
Wire cross-section, AWG, min.	AWG 28	Wire cross-section, AWG, max.	AWG 12
Reference to approval values	Specifications are maximum values, details -		

#### **Packing**

Packaging	Box	VPE length	349.00 mm
VPE width	135.00 mm	VPE height	32.00 mm

#### Type tests

Test: Durability of markings	Standard	DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96	
	Test	mark of origin, type identification, pitch, type of material, date clock	
	Evaluation	available	
	Test	durability	
	Evaluation	passed	
Test: Misengagement (Non-	Standard	DIN EN 61984 section 6.3 and 6.9.1 / 09.02	
interchangeability)	Test	180° turned with coding elements	
	Evaluation	passed	
	Test	180° turned without coding elements	
	Evaluation	passed	
Test: Clampable cross section	Standard	DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02	
	Conductor type	Type of conductor solid 0.5 mm <sup>2</sup> and conductor cross-section	

Creation date 28.11.2025 04:59:52 MEZ



## Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

		Type of conductor stranded 0.5 mm <sup>2</sup> and conductor cross-section
		Type of conductor solid 2.5 mm <sup>2</sup> and conductor cross-section
		Type of conductor stranded 2.5 mm <sup>2</sup> and conductor cross-section
		Type of conductor AWG 20/1 and conductor cross-section
		Type of conductor AWG 20/19 and conductor cross-section
		Type of conductor AWG 12/1 and conductor cross-section
		Type of conductor AWG 12/19 and conductor cross-section
	Evaluation	passed
Test for damage to and accidental	Standard	DIN EN 60999-1 section 9.4 / 12.00
posening of conductors	Requirement	0.2 kg
	Conductor type	Type of conductor AWG 28/1 and conductor cross-section
		Type of conductor AWG 28/19 and conductor cross-section
	Evaluation	passed
	Requirement	0.3 kg
	Conductor type	Type of conductor H05V-U0.5 and conductor cross-section
		Type of conductor H05V-K0.5 and conductor cross- section
	Evaluation	passed
	Requirement	0.7 kg
	Conductor type	Type of conductor AWG 14/1 and conductor cross-section
		Type of conductor AWG 14/19 and conductor cross-section
	Evaluation	passed
	Requirement	0.9 kg
	Conductor type	Type of conductor H07V-U4.0 and conductor cross-section
		Type of conductor H07V-K4.0 and conductor cross-section
	Evaluation	passed
ull-out test	Standard	DIN EN 60999-1 section 9.5 / 12.00
	Requirement	≥5 N
	Conductor type	Type of conductor AWG 28/1 and conductor cross-section
		Type of conductor AWG 28/19 and conductor cross-section

Creation date 28.11.2025 04:59:52 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Evaluation	passed		
Requirement	≥20 N		
Conductor type	Type of conductor and conductor cross-section	H05V-U0.5	
	Type of conductor and conductor cross-section	H05V-K0.5	
Evaluation	passed		
Requirement	≥50 N		
Conductor type	Type of conductor and conductor cross-section	AWG 14/1	
	Type of conductor and conductor cross-section	AWG 14/19	
	Type of conductor and conductor cross-section	H07V-K4.0	
Evaluation	passed		
Requirement	≥60 N		
Conductor type	Type of conductor and conductor cross-section	H07V-U4.0	
Evaluation	passed		

#### Important note

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- · Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- $\bullet$  Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

#### Classifications

ETIM 6.0	EC002638	ETIM 7.0	EC002638
ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 9.0	27-44-03-09
ECLASS 9.1	27-44-03-09	ECLASS 10.0	27-44-03-09
ECLASS 11.0	27-46-02-02	ECLASS 12.0	27-46-02-02
ECLASS 13.0	27-46-02-02	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		

Creation date 28.11.2025 04:59:52 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

# **Drawings**

## **Product image**



## **Dimensional drawing**



Graph Graph

